



FAG

6022-M-C4

Deep groove ball bearing

Deep groove ball bearing 60...-M, single row, solid brass cage

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	M	Solid brass cage, rolling element guided
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	Without	Bearing not greased
Radial internal clearance	C4 (Group 4)	Internal clearance larger than C3
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	110 mm	Bore diameter
D	170 mm	Outside diameter
B	28 mm	Width
C _r	85,000 N	Basic dynamic load rating, radial
C _{0r}	71,000 N	Basic static load rating, radial
C _{ur}	3,550 N	Fatigue load limit, radial
n _G	6,900 1/min	Limiting speed
n _{gr}	4,850 1/min	Reference speed
≈m	2.42 kg	Weight



Mounting dimensions

d _{a min}	118.8 mm	Minimum diameter shaft shoulder
D _{a max}	161.2 mm	Maximum diameter of housing shoulder
r _{a max}	2 mm	Maximum fillet radius

Dimensions

r _{min}	2 mm	Minimum chamfer dimension
D ₁	151.02 mm	Shoulder diameter outer ring
d ₁	129.12 mm	Shoulder diameter inner ring







Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	150 °C	Operating temperature max.

Calculation factors

f ₀	15.7	Calculation factor
----------------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed