



Pushing Performance
Since 1945

D SUB IP 67 FE STR_PCB_50P_S4_METAL FRAM



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 650 6775
Specification	D SUB IP 67 FE STR_PCB_50P_S4_METAL FRAM
HARTING eCatalogue	https://harting.com/09676506775

Identification

Category	Connectors
Series	D-Sub
Identification	IP67
Element	Connector
Specification	With rear frame
Description of the contact	Turned Straight

Version

Termination method	Wave soldering termination
Gender	Female
Size	D-Sub 5
Number of contacts	50
further contacts	With grounding pin
PCB fixing	With board locks
Locking type	Fixing flange with thread 4-40 UNC

Technical characteristics

Distance between rows	2.84 mm
Contact spacing (termination side)	2.74 mm
Rated current	5 A
Clearance distance	≥1 mm
Creepage distance	≥1 mm



Pushing Performance
Since 1945

Technical characteristics

Insulation resistance	$> 5 \times 10^9 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	0.4 ... 0.6 Nm Female screw lock
Limiting temperature	-25 ... +70 °C
Performance level	NM 30 (S4) 1
Mating cycles	≥ 500
Degree of protection acc. to IEC 60529	IP67
Test voltage $U_{r.m.s.}$	1.2 kV
Isolation group	IIIa ($175 \leq CTI < 400$)
PCB thickness	1.6 mm
Installation height	8 mm
Hot plugging	No

Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled Shell: brass, tin plated
Colour (insert)	Red
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni
Layer thickness	$\geq 0.76 \mu\text{m}$
Layer thickness	$\geq 30 \mu\text{inch}$
Material (seal)	Silicone
Colour (seal)	Red
Material	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance
Since 1945

Material properties

ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Specifications and approvals

Specifications	DIN 41652
UL / CSA	UL 1977 ECBT2.E102079

Commercial data

Packaging size	25
Net weight	51.36 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140095090
eCl@ss	27440214 D-Sub coupler
ETIM	EC001136
UNSPSC 24.0	39121469