

Hedge Trimmer XGT®

UH013G

40Vmax • 600 mm

Efficient brushless Trimmer for professional use.

Professional XGT® Hedge Trimmer with brushless motor. The blade is single-sided for a lightweight and ergonomic design.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	2000 / 3600 / 5000 min ⁻¹
Length Of Blade	600 mm
Max blade opening	23,5 mm
Tooth Spacing	35 mm
Continuous Use XGT® 40V Max / 4.0 Ah	85 / 160 / 390
Brushless Motor	✓
Sound Power Level (L _{WA})	91 dB(A)
Sound Pressure Level (L _{pA})	83 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	2,5 / 2,5 m/s ²
Vibration Uncertainty (K Factor), Hedge Trimming	1,5 m/s ²

User benefits

- Lightweight for reduced operator fatigue
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Double action switch for increased safety
- Reverse rotation system frees the blade when it is jammed by thick branches
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing