



SAFETY DATA SHEET AF SPRAY 200ML

RS REACH revision date 01/03/11

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME AF SPRAY 200ML
PRODUCT NO. AFS200 [AAFS200]
APPLICATION Cleaning Product
SUPPLIER AF INTERNATIONAL. A division
of HK WENTWORTH LTD
KINGSBURY PARK.
MIDLAND ROAD,
SWADLINCOTE
DERBYSHIRE DE11 0AN
UNITED KINGDOM
+44 (0) 1283 222111
+44 (0) 1283 550177
info@hkw.co.uk

Supplied by:
RS Components Ltd,
Birchington Road, Corby, Northants, NN17 9RS.
Tel: +44 (0) 1536 402888 (8am to 8pm)
Email: technical.help@rs-components.com

EMERGENCY TELEPHONE +44(0)1283 222 111 between 8.30 am - 5.00pm Mon - Fri

2 HAZARDS IDENTIFICATION

Extremely flammable.

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Repeated exposure may cause skin dryness or cracking.

Vapours may cause drowsiness and dizziness.

CLASSIFICATION F+;R12. N;R51/53. R66, R67.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
PENTANE	203-692-4	109-66-0	80-100%	F+;R12 Xn;R65 R66 R67 N;R51/53
PROPAN-2-OL	200-661-7	67-63-0	10-30%	F;R11 Xi;R36 R67

The Full Text for all R-Phrases are Displayed in Section 16

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention. Get medical attention.

INGESTION

Immediately rinse mouth and provide fresh air.

SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

AF SPRAY 200ML

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

SPECIAL FIRE FIGHTING PROCEDURES

Move container from fire area if it can be done without risk.

UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Absorb in vermiculite, dry sand or earth and place into containers. Ventilate well.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Avoid spilling, skin and eye contact. Provide good ventilation.

STORAGE PRECAUTIONS

Store at moderate temperatures in dry, well ventilated area.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	TWA - 8 hrs		STEL - 15 min		Notes
PENTANE	WEL	600 ppm	1800 mg/m3			
PROPAN-2-OL	WEL	400 ppm	999 mg/m3	500 ppm	1250 mg/m3	

WEL = Workplace Exposure Limit.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

HYGIENE MEASURES

Wash at the end of each work shift and before eating, smoking and using the toilet. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke. **DO NOT SMOKE IN WORK AREA!**

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Aerosol Liquid		
COLOUR	Colourless		
ODOUR	Characteristic		
PHYSICAL DATA COMMENTS	Information given concerns the major ingredient.		
VOLATILITY DESCRIPTION	Volatile.		
SOLUBILITY	Immiscible with water		
BOILING POINT (°C)	36	MELTING POINT (°C)	-130
RELATIVE DENSITY	0.650 @ 20 °c	BULK DENSITY	650 kg/m3
VAPOUR PRESSURE	5.33 kPa @ 19 °c	FLASH POINT (°C)	- 48 CC (Closed cup).
AUTO IGNITION	309	FLAMMABILITY LIMIT - LOWER(%)	1.4
TEMPERATURE (°C)			
FLAMMABILITY LIMIT - UPPER(%)	7.8		

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with acids and alkalies.

11 TOXICOLOGICAL INFORMATION

AF SPRAY 200ML

INHALATION

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. High concentrations of vapours may irritate respiratory system and lead to headache, fatigue, nausea and vomiting.

SKIN CONTACT

Product has a defatting effect on skin. Prolonged contact may cause dryness of the skin. Prolonged or repeated exposure may cause severe irritation.

EYE CONTACT

Irritating to eyes.

OTHER HEALTH EFFECTS

This substance has no evidence of carcinogenic properties.

ROUTE OF ENTRY

Inhalation.

Name	PENTANE
Toxic Dose 1 - LD 50	>2000 mg/kg (oral rat)
Toxic Dose 2 - LD 50	446 mg/kg (ivn-mouse)
Toxic Conc. - LC 50	364,000 mg/m ³ /30h (inh-rat)
Name	PROPAN-2-OL
Toxic Dose 1 - LD 50	5045 mg/kg (oral rat)
Toxic Dose 2 - LD 50	3600 mg/kg (oral-mouse)
Toxic Conc. - LC 50	47-73 mg/l/4h (inh-rat)

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

Name	PENTANE
	PROPAN-2-OL
LC 50, 96 Hrs, FISH mg/l	9600
EC 50, 48 Hrs, DAPHNIA, mg/l	10000

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION



UK ROAD CLASS	2		
PROPER SHIPPING NAME	AEROSOLS (PENTANE)		
UN NO. ROAD	1950	UK ROAD PACK GR.	N/A
ADR CLASS NO.	2	ADR CLASS	Class 2: Gases
ADR PACK GROUP	N/A	TUNNEL RESTRICTION CODE	(D)
ADR LABEL NO.	2.1	CEFIC TEC(R) NO.	20G5F
RID CLASS NO.	2	RID PACK GROUP	N/A
UN NO. SEA	1950	IMDG CLASS	2.1
IMDG PACK GR.	N/A	EMS	F-D, S-U
MFAG	See Guide	MARINE POLLUTANT	No.
UN NO. AIR	1950	AIR CLASS	2.1
AIR PACK GR.	N/A		

AF SPRAY 200ML

15 REGULATORY INFORMATION

SYMBOLS



Extremely Flammable



Dangerous for the environment

RISK PHRASES

R12	Extremely flammable.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

SAFETY PHRASES

S16	Keep away from sources of ignition - No smoking.
S51	Use only in well-ventilated areas.
A1	Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2	Do not spray on a naked flame or any incandescent material.
S2	Keep out of the reach of children

UK REGULATORY REFERENCES

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 1988.

ENVIRONMENTAL LISTING

Rivers (Prevention of Pollution) Act 1961. Control of Pollution Act 1974.

EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

STATUTORY INSTRUMENTS

Control of Substances Hazardous to Health.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

GUIDANCE NOTES

Workplace Exposure Limits EH40.

16 OTHER INFORMATION

REVISION COMMENTS

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

ISSUED BY

Helen O'Reilly

REVISION DATE

NOVEMBER 2009

AF SPRAY 200ML

REV. NO./REPL. SDS 5
GENERATED
SDS NO. 10630

RISK PHRASES IN FULL

- R11 Highly flammable.
- R12 Extremely flammable.
- R36 Irritating to eyes.
- R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R65 Harmful: may cause lung damage if swallowed.
- R66 Repeated exposure may cause skin dryness or cracking.
- R67 Vapours may cause drowsiness and dizziness.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.