

# PRODUCT DATASHEET

## HQL LED HIGHBAY 250 115 ° 95 W/4000 K E40

HQL LED HIGHBAY | LED replacement for HID lamps for high-bay luminaires



### Areas of application

- LED alternative for applications requiring a high luminous flux
- Industrial and storage facilities
- Outdoor applications only in suitable luminaires

### Product benefits

- Energy savings of up to 65 % when replacing mercury vapor lamps (HQL)
- Effective thermal management for wide operating temperature range
- Low maintenance costs thanks to long lifetime
- Instant 100 % light, no warm-up time

### Product features

- Replacement for HQL: Suitable for operation with conventional control gear (CCG) for HQL or 230 V mains
- Replacement for other HID: Suitable for operation with line voltage without control gear
- Power factor: 0.9
- Type of protection: IP40
- High surge protection: up to 4 kV (L-N)




## TECHNICAL DATA

### Electrical data

Nominal wattage	95 W
Construction wattage	95.00 W
Nominal voltage	220...240 V
Claimed equiv. conventional lamp power	250 W
Nominal current	450 mA
Type of current	AC
Inrush current	23 A
Operating frequency	50/60 Hz
Mains frequency	50/60 Hz
Max. lamp no. on circuit break. 10 A (B)	7
Max. lamp no. on circuit break. 16 A (B)	11
Total harmonic distortion	< 25 %
Power factor $\lambda$	> 0.90

### Photometrical data


Luminous flux	13000 lm
Nominal useful luminous flux 90°	13000 lm
Luminous efficacy	136 lm/W
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Cool White
Color temperature	4000 K
Color rendering index Ra	80
Light color	840
Standard deviation of color matching	$\leq 6$ sdcn
Rated LLMF at 6,000 h	0.80
Flickering metric (Pst LM)	1.0
Stroboscope effect metric (SVM)	0.4



### Light technical data

Beam angle	115 °
Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s
Rated beam angle (half peak value)	115.00 °

### Dimensions & Weight



Overall length	275.00 mm
Diameter	190.00 mm
Maximum diameter	190 mm
Product weight	760.00 g

### Temperatures & operating conditions

Ambient temperature range	-20...+50 °C
Maximum temperature at tc test point	100 °C

### Lifespan

Nominal lamp life time	50000 h
Number of switching cycles	100000
Lumen maintenance at end of serv	0.70
Rated lamp survival factor at 6,000	0.90

### Additional product data

Base (standard designation)	E40
Mercury content	0.0 mg

## Capabilities

Dimmable	No
----------	----

## Certificates & Standards

Energy efficiency class	E
Energy consumption	95.00 kWh/1000h
Type of protection	IP40
Standards	CE / EAC
Photobiological safety group acc. to EN62778	RG1

## Country-specific categorizations

Order reference	HQLEDHB13000 95
-----------------	-----------------

## Energy labelling regulation data acc EU 2019/2015

Lighting technology used	LED
Non-directional or directional	NDLS
Mains or non-mains	MLS
Light source cap-type (or other electric interface)	E40
Connected light source (CLS)	No
Color-tuneable light source	No
Envelope	No
High luminance light source	No
Anti-glare shield	No
Correlated colour temperature type	SINGLE_VALUE
Claim of equivalent power	No
Length	278.00 mm
Height	190.00 mm
Width	190.00 mm
Chromaticity coordinate x	0.381
Chromaticity coordinate y	0.379
Beam angle	SPHERE_360
Survival factor	0.90
Displacement factor	0.90
LED light source replaces a fluorescent light source	not applicable
EPREL ID	567213
Model number	AC35213

## EQUIPMENT / ACCESSORIES

- Safety sling for lamp included

## Safety advice

- The bulb may be larger and heavier than the replaced bulb. Before installation it must be checked, if the luminaire and especially the holder is capable of carrying the weight of the lamp. Safety sling has to be installed.
- Only suitable for temperatures of up to 50°C inside of the luminaire.
- Not suitable for operation with ignitors
- Operation on the capacitor can lead to a reduction of the power factor of the system.
- To ensure full light efficiency and product lifetime, it is recommended to detach any glass or cover of the luminaire.

## DOWNLOAD DATA

### DOWNLOAD DATA



User instruction  
User Instruction OSRAM HQL LED Highbay

## LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075612594	Folding box 1	202 mm x 202 mm x 293 mm	892.00 g	11.96 dm <sup>3</sup>
4058075612600	Shipping box 4	420 mm x 420 mm x 315 mm	4549.00 g	55.57 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.