

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Eight MINI Analog Pro signal conditioners and measuring transducers are quickly and easily integrated into a PROFIBUS DP network via a communication adapter.

## Product description

Thanks to its innovative plug-in concept, the communication adapter offers a time-saving wiring solution. Eight MINI Analog Pro signal converters can be quickly and easily integrated into a PROFIBUS DP network using a communication adapter. Flexible signal combinations and eliminating the need for I/O input cards saves space and money in the control cabinet.

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 2905636             |
| Packing unit                         | 1 pc                |
| Minimum order quantity               | 1 pc                |
| Sales key                            | CK1                 |
| Product key                          | DK112Z              |
| Catalog page                         | Page 100 (C-5-2019) |
| GTIN                                 | 4046356996723       |
| Weight per piece (including packing) | 199.5 g             |
| Weight per piece (excluding packing) | 136 g               |
| Customs tariff number                | 85176200            |
| Country of origin                    | DE                  |

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## Technical data

### Notes

#### Utilization restriction

|          |                                                                           |
|----------|---------------------------------------------------------------------------|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---------------------------------------------------------------------------|

### Product properties

|                |                      |
|----------------|----------------------|
| Product type   | Communication module |
| Product family | MINI Analog Pro      |

#### Insulation characteristics: GB Standard

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree     | 2  |

### Electrical properties

|                                   |                     |
|-----------------------------------|---------------------|
| Rated insulation voltage          | 50 V <sub>rms</sub> |
| Test voltage, input/output/supply | 0.5 kV              |
| Maximum temperature coefficient   | 0.01 %              |
| Maximum transmission error        | 0.1 %               |

#### Supply

|                              |                      |
|------------------------------|----------------------|
| Nominal supply voltage range | 12 V ... 24 V        |
| Supply voltage range         | 9.6 V ... 30 V       |
| Typical current consumption  | 160 mA (at 9.6 V DC) |
| Power consumption            | < 700 mW             |

### Input data

|                                |                         |
|--------------------------------|-------------------------|
| Available input sources        | floating switch contact |
|                                | Current source          |
| Number of inputs               | 8                       |
| Configurable/programmable      | Yes                     |
| Current input signal           | 4 mA ... 20 mA          |
| Maximum input current          | 24 mA                   |
| Input resistance current input | 50 Ω                    |
| Maximum input voltage          | 5 V                     |

### Output data

|                           |             |
|---------------------------|-------------|
| Protocols supported       | PROFIBUS DP |
| Number of outputs         | 1           |
| Configurable/programmable | Yes         |
| Transmission speed        | 12 Mbps     |
| Data update rate          | 15 ms       |

### Connection data

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## Output

|                     |                    |
|---------------------|--------------------|
| Connection method   | D-SUB socket strip |
| Number of positions | 9                  |

## Ex data

|                       |        |
|-----------------------|--------|
| Ex installation (EPL) | Gc     |
|                       | Div. 2 |

## Signaling

|                  |             |
|------------------|-------------|
| Status display   | LED (green) |
| Error indication | Red LED     |

## Dimensions

|        |          |
|--------|----------|
| Width  | 51.1 mm  |
| Height | 104.1 mm |
| Depth  | 56.8 mm  |

## Material specifications

|                  |                 |
|------------------|-----------------|
| Color            | gray (RAL 7042) |
| Housing material | PBT 7 % GF V0   |

## Environmental and real-life conditions

### Ambient conditions

|                                          |                      |
|------------------------------------------|----------------------|
| Degree of protection                     | IP20 (Finger safety) |
| Ambient temperature (operation)          | -40 °C ... 60 °C     |
| Ambient temperature (storage/transport)  | -40 °C ... 70 °C     |
| Altitude                                 | 4000 m               |
| Permissible humidity (operation)         | 5 % ... 95 %         |
| Permissible humidity (storage/transport) | 5 % ... 95 %         |

## Approvals

### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

### ATEX

|                |                          |
|----------------|--------------------------|
| Identification | Ⓔ II 3 G Ex ec IIC T4 Gc |
| Certificate    | BVS 21 ATEX E 064 X      |

### UKCA Ex (UKEX)

|                |                          |
|----------------|--------------------------|
| Identification | Ⓔ II 3 G Ex ec IIC T4 Gc |
| Certificate    | PxCIF21UKEX2905634X      |

### IECEX

|                |                    |
|----------------|--------------------|
| Identification | Ex ec IIC T4 Gc    |
| Certificate    | IECEX BVS 21.0071X |

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## CCC / China-Ex

|                |                  |
|----------------|------------------|
| Identification | Ex ec IIC T4 Gc  |
| Certificate    | 2022122308115724 |

## UL, USA/Canada

|                |                                       |
|----------------|---------------------------------------|
| Identification | UL 508 Listed                         |
|                | Class I, Div. 2, Groups A, B, C, D T5 |
|                | Class I, Zone 2, Group IIC T5         |

## EAC Ex

|                |                                 |
|----------------|---------------------------------|
| Identification | Ex ec IIC T4 Gc                 |
| Certificate    | BY/112 02.01 TP012 103.01 00081 |

## EMC data

|                               |                                                                      |
|-------------------------------|----------------------------------------------------------------------|
| Electromagnetic compatibility | Conformance with EMC directive                                       |
| Noise immunity                | EN 61000-6-2                                                         |
| Note                          | When being exposed to interference, there may be minimal deviations. |
| Noise emission                | EN 61000-6-4                                                         |

## Standards and regulations

### GB Standard

|                       |             |
|-----------------------|-------------|
| Standards/regulations | GB/T 3836.1 |
|                       | GB/T 3836.3 |

## Mounting

|                   |                  |
|-------------------|------------------|
| Mounting type     | Plug-on assembly |
| Mounting position | any              |

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/2905636>



**EAC**

Approval ID: RU\*DE.\*08.B.01518/19



**UL Listed**

Approval ID: E238705



**cUL Listed**

Approval ID: E238705

**PROFIBUS**

Approval ID: Z02107



**cUL Listed**

Approval ID: E196811



**UL Listed**

Approval ID: E196811



**CCC**

Approval ID: 2022122308115724

**cULus Listed**

**cULus Listed**

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27242608 |
| ECLASS-12.0 | 27242608 |
| ECLASS-13.0 | 27242608 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001604 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 32151600 |
|-------------|----------|

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes                |
| Exemption                               | 6(c), 7(a), 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | f7d2bfdd-79b8-4b89-9792-fb1b96c473db |

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## Accessories

### MINI MCR-2-PTB - Power terminal block

2902066

<https://www.phoenixcontact.com/in/products/2902066>



Power terminal with plug-in connection technology for delivering the supply voltage to the DIN rail connector. Monitoring of the supply voltages in combination with the fault monitoring module. Screw connection technology

---

### MINI MCR-2-PTB-PT - Power terminal block

2902067

<https://www.phoenixcontact.com/in/products/2902067>



Power terminal with plug-in connection technology for delivering the supply voltage to the DIN rail connector. Monitoring of the supply voltages in combination with the fault monitoring module. Push-in connection technology

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-TB - Feed-through terminal block

2902068

<https://www.phoenixcontact.com/in/products/2902068>



Feed-through terminal block with plug-in connection technology for the transmission of signals already electrically isolated. Screw connection technology

---

## MINI MCR-2-FM-RC - Monitoring block

2904504

<https://www.phoenixcontact.com/in/products/2904504>



Fault monitoring module with plug-in connection technology for evaluating and reporting group errors from the FM system and for monitoring the supply voltages. Error message via N/C contact. Screw connection technology, standard configuration

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-FM-RC-PT - Monitoring block

2904508

<https://www.phoenixcontact.com/in/products/2904508>



Fault monitoring module with plug-in connection technology for evaluating and reporting group errors from the FM system and for monitoring the supply voltages. Error message via N/C contact. Push-in connection technology, standard configuration

---

## MINI MCR-2-UNI-UI-UIRO-PT - Signal conditioner

2902028

<https://www.phoenixcontact.com/in/products/2902028>



Universally configurable 4-way signal conditioner, with switching output and plug-in connection technology for the electrical isolation of analog signals. Configurable via DIP switch or software. Push-in connection technology, standard configuration.

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-UNI-UI-UIRO - Signal conditioner

2902026

<https://www.phoenixcontact.com/in/products/2902026>



Universally configurable 4-way signal conditioner, with switching output and plug-in connection technology for the electrical isolation of analog signals. Configurable via DIP switch or software. Screw connection technology, standard configuration.

---

## MINI MCR-2-UNI-UI-UIRO-PT-C - Signal conditioner

2902027

<https://www.phoenixcontact.com/in/products/2902027>



Universally configurable 4-way signal conditioner, with switching output and plug-in connection technology for the electrical isolation of analog signals. Configurable via DIP switch or software. Push-in connection technology, order configuration.

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-UNI-UI-UIRO-C - Signal conditioner

2902024

<https://www.phoenixcontact.com/in/products/2902024>



Universally configurable 4-way signal conditioner, with switching output and plug-in connection technology for the electrical isolation of analog signals. Configurable via DIP switch or software. Screw connection technology, order configuration.

---

## MINI MCR-2-UI-UI-PT - Signal conditioner

2902040

<https://www.phoenixcontact.com/in/products/2902040>



3-way signal conditioner with plug-in connection technology and calibrated measuring range changeover, for the electrical isolation of unipolar and bipolar analog signals. Input/output configurable via DIP switch. push-in connection technology, standard configuration.

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-UI-UI - Signal conditioner

2902037

<https://www.phoenixcontact.com/in/products/2902037>




3-way signal conditioner with plug-in connection technology and calibrated measuring range changeover for the electrical isolation of unipolar and bipolar analog signals. Input/output configurable via DIP switch. Screw connection technology, standard configuration.

---

## MINI MCR-2-UI-UI-PT-C - Signal conditioner

2902039

<https://www.phoenixcontact.com/in/products/2902039>



3-way signal conditioner with plug-in connection technology and calibrated measuring range changeover for the electrical isolation of unipolar and bipolar analog signals. Input/output configurable via DIP switch. push-in connection technology, order configuration.

# MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-UI-UI-C - Signal conditioner

2902036

<https://www.phoenixcontact.com/in/products/2902036>



3-way signal conditioner with plug-in connection technology and calibrated measuring range changeover for the electrical isolation of unipolar and bipolar analog signals. Input/output configurable via DIP switch. Screw connection technology, order configuration.

---

## MINI MCR-2-U-UI-PT - Signal conditioner

2902021

<https://www.phoenixcontact.com/in/products/2902021>



3-way signal conditioner, with configurable input/output, for electrical isolation and conversion of analog signals in the mV and V range, unipolar as well as bipolar. Push-in connection technology, standard configuration.

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-U-UI - Signal conditioner

2902019

<https://www.phoenixcontact.com/in/products/2902019>



3-way signal conditioner, with configurable input/output, for electrical isolation and conversion of analog signals in the mV and V range, unipolar as well as bipolar. Screw connection technology, standard configuration.

---

## MINI MCR-2-U-I0-PT - Signal conditioner

2902023

<https://www.phoenixcontact.com/in/products/2902023>



3-way signal conditioner with plug-in connection technology for the electrical isolation of analog signals. Input signal: 0 V ... 10 V, output signal: 0 mA ... 20 mA, push-in connection technology

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-U-I0 - Signal conditioner

2902022

<https://www.phoenixcontact.com/in/products/2902022>



3-way signal conditioner with plug-in connection technology for the electrical isolation of analog signals. Input signal: 0 V ... 10 V, output signal: 0 mA ... 20 mA, screw connection technology

---

## MINI MCR-2-U-I4-PT - Signal conditioner

2902030

<https://www.phoenixcontact.com/in/products/2902030>



3-way signal conditioner with plug-in connection technology for the electrical isolation of analog signals. Input signal: 0 V ... 10 V, output signal: 4 mA ... 20 mA, push-in connection technology

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-U-I4 - Signal conditioner

2902029

<https://www.phoenixcontact.com/in/products/2902029>



3-way signal conditioner with plug-in connection technology for the electrical isolation of analog signals. Input signal: 0 V ... 10 V, output signal: 4 mA ... 20 mA, screw connection technology

---

## MINI MCR-2-I-I-PT - Signal conditioner

2901999

<https://www.phoenixcontact.com/in/products/2901999>



3-way signal conditioner with plug-in connection technology for the electrical isolation of analog signals. Input signal: 0(4) mA ... 20 mA, output signal: 0(4) mA ... 20 mA, push-in connection technology.

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-I-I - Signal conditioner

2901998

<https://www.phoenixcontact.com/in/products/2901998>



3-way signal conditioner with plug-in connection technology for the electrical isolation of analog signals. Input signal: 0(4) mA ... 20 mA, output signal: 0(4) mA ... 20 mA, screw connection technology

---

## MINI MCR-2-UNI-UI-2UI-PT - Signal duplicator

2905028

<https://www.phoenixcontact.com/in/products/2905028>



Universally configurable 4-way signal duplicator, with plug-in connection technology for the electrical isolation and duplication of analog signals. Configurable via DIP switch or software. Push-in connection technology, standard configuration.

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-UNI-UI-2UI - Signal duplicator

2905026

<https://www.phoenixcontact.com/in/products/2905026>



Universally configurable 4-way signal duplicator, with plug-in connection technology for the electrical isolation and duplication of analog signals. Configurable via DIP switch or software. Screw connection technology, standard configuration.

---

## MINI MCR-2-UNI-UI-2UI-PT-C - Signal duplicator

2905027

<https://www.phoenixcontact.com/in/products/2905027>



Universally configurable 4-way signal duplicator, with plug-in connection technology for the electrical isolation and duplication of analog signals. Configurable via DIP switch or software. Push-in connection technology, order configuration.

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-UNI-UI-2UI-C - Signal duplicator

2905025

<https://www.phoenixcontact.com/in/products/2905025>



Universally configurable 4-way signal duplicator, with plug-in connection technology for the electrical isolation and duplication of analog signals. Configurable via DIP switch or software. Screw connection technology, order configuration.

---

## MINI MCR-2-RPSS-I-I-PT - Repeater power supply

2902015

<https://www.phoenixcontact.com/in/products/2902015>



3-way repeater power supply with plug-in connection technology. HART-transparent, input signal 0(4) mA ... 20 mA, output signal 0(4) mA ... 20 mA. The device can be used in both isolator and repeater power supply operation. push-in connection technology

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-RPSS-I-I - Repeater power supply

2902014

<https://www.phoenixcontact.com/in/products/2902014>



3-way repeater power supply with plug-in connection technology. HART-transparent, input signal 0(4)...20 mA, output signal 0(4)...20 mA. The device can be used in both isolator and repeater power supply operation. Screw connection technology

---

## MINI MCR-2-RPSS-I-2I-PT - Repeater power supply

2905629

<https://www.phoenixcontact.com/in/products/2905629>



4-way power supply doubler with plug-in connection technology. HART-transparent, 0(4) mA ... 20 mA input signal, 0(4) mA ... 20 mA output signals. The device can be used in both signal and power supply doubler modes. Push-in connection technology.

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-RPSS-I-2I - Repeater power supply

2905628

<https://www.phoenixcontact.com/in/products/2905628>



4-way power supply doubler with plug-in connection technology. HART-transparent, 0(4) mA ... 20 mA input signal, 0(4) mA ... 20 mA output signals. The device can be used in both signal and power supply doubler modes. Screw connection technology.

---

## MINI MCR-2-I-I-ILP-PT - Passive separator

2901995

<https://www.phoenixcontact.com/in/products/2901995>



1-channel input loop-powered 2-way isolator with plug-in connection technology for the electrical isolation of analog signals. Input signal = output signal: 0(4) mA ... 20 mA. Push-in connection technology.

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-I-I-ILP - Passive separator

2901994

<https://www.phoenixcontact.com/in/products/2901994>



1-channel input loop-powered 2-way isolator with plug-in connection technology for the electrical isolation of analog signals. Input signal = output signal: 0(4) mA ... 20 mA. Screw connection technology.

---

## MINI MCR-2-RTD-UI-PT - Resistance thermometer measuring transducer

2902052

<https://www.phoenixcontact.com/in/products/2902052>



Configurable temperature transducer with plug-in connection technology for connecting 2, 3, and 4-conductor resistance thermometers and resistance-type sensors. Configurable via DIP switch or software. push-in connection technology, standard configuration

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-RTD-UI - Resistance thermometer measuring transducer

2902049

<https://www.phoenixcontact.com/in/products/2902049>



Configurable temperature transducer with plug-in connection technology for connecting 2, 3, and 4-conductor resistance thermometers and resistance-type sensors. Configurable via DIP switch or software. Screw connection technology, standard configuration

---

## MINI MCR-2-RTD-UI-PT-C - Resistance thermometer measuring transducer

2902051

<https://www.phoenixcontact.com/in/products/2902051>



Configurable temperature transducer with plug-in connection technology for connecting 2, 3, and 4-conductor resistance thermometers and resistance-type sensors. Configurable via DIP switch or software. push-in connection technology, order configuration

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-RTD-UI-C - Resistance thermometer measuring transducer

2902048

<https://www.phoenixcontact.com/in/products/2902048>



Configurable temperature transducer with plug-in connection technology for connecting 2, 3, and 4-conductor resistance thermometers and resistance-type sensors. Configurable via DIP switch or software. Screw connection technology, order configuration

---

## MINI MCR-2-TC-UI-PT - Thermocouple measuring transducer

2905249

<https://www.phoenixcontact.com/in/products/2905249>



Configurable temperature transducer with plug-in connection technology for connecting thermocouples. Configurable via DIP switch or software. Push-in connection technology, standard configuration

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-TC-UI - Thermocouple measuring transducer

2902055

<https://www.phoenixcontact.com/in/products/2902055>



Configurable temperature transducer with plug-in connection technology for connecting thermocouples. Configurable via DIP switch or software. Screw connection technology, standard configuration

---

## MINI MCR-2-TC-UI-PT-C - Thermocouple measuring transducer

2905248

<https://www.phoenixcontact.com/in/products/2905248>



Configurable temperature transducer with plug-in connection technology for connecting thermocouples. Configurable via DIP switch or software. Push-in connection technology, order configuration

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-TC-UI-C - Thermocouple measuring transducer

2902053

<https://www.phoenixcontact.com/in/products/2902053>



Configurable temperature transducer with plug-in connection technology for connecting thermocouples. Configurable via DIP switch or software. Screw connection technology, order configuration

---

## MINI MCR-2-T-REL-PT - Limit value switch

2905633

<https://www.phoenixcontact.com/in/products/2905633>



Universally configurable temperature limit value switch with N/O relay output for the connection of 2, 3, and 4-conductor resistance thermometers and thermocouples. Configurable via DIP switch or software. Push-in connection technology

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-T-REL - Limit value switch

2905632

<https://www.phoenixcontact.com/in/products/2905632>



Universally configurable temperature limit value switch with N/O relay output for the connection of 2, 3, and 4-conductor resistance thermometers and thermocouples. Configurable via DIP switch or software, screw connection technology

---

## MINI MCR-2-UI-FRO-PT - Frequency measuring transducer

2902032

<https://www.phoenixcontact.com/in/products/2902032>



Analog frequency transducer with limit value functionality and plug-in connection technology for converting standard signals into frequency or PWM signals. Configurable via DIP switch or software. Push-in connection technology, standard configuration.

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-UI-FRO - Frequency measuring transducer

2902031

<https://www.phoenixcontact.com/in/products/2902031>



Analog frequency transducer with limit value functionality and plug-in connection technology for converting standard signals into frequency or PWM signals. Configurable via DIP switch or software. Screw connection technology, standard configuration.

---

## MINI MCR-2-UI-FRO-PT-C - Frequency measuring transducer

2906202

<https://www.phoenixcontact.com/in/products/2906202>



Analog frequency transducer with limit value functionality and plug-in connection technology for converting standard signals into frequency or PWM signals. Configurable via DIP switch or software. Push-in connection technology, order configuration.

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-UI-FRO-C - Frequency measuring transducer

2906201

<https://www.phoenixcontact.com/in/products/2906201>



Analog frequency transducer with limit value functionality and plug-in connection technology for converting standard signals into frequency or PWM signals. Configurable via DIP switch or software. Screw connection technology, order configuration.

---

## MINI MCR-2-POT-UI-PT - Resistance/potiposition transducer

2902017

<https://www.phoenixcontact.com/in/products/2902017>



Configurable potiposition transducer with plug-in connection technology for connecting potentiometers from 0  $\Omega$  ... 100  $\Omega$  to 0 k $\Omega$  ... 100 k $\Omega$ . Configurable via DIP switch or software. push-in connection technology, standard configuration

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-POT-UI - Resistance/potiposition transducer

2902016

<https://www.phoenixcontact.com/in/products/2902016>



Configurable potiposition transducer with plug-in connection technology for connecting potentiometers from 0  $\Omega$  ... 100  $\Omega$  to 0 k $\Omega$  ... 100 k $\Omega$ . Configurable via DIP switch or software. Screw connection technology, standard configuration

---

## MINI MCR-2-POT-UI-PT-C - Resistance/potiposition transducer

2905006

<https://www.phoenixcontact.com/in/products/2905006>



Configurable potiposition transducer with plug-in connection technology for connecting potentiometers from 0  $\Omega$  ... 100  $\Omega$  to 0 k $\Omega$  ... 100 k $\Omega$ . Configurable via DIP switch or software. Push-in connection technology, order configuration

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-POT-UI-C - Resistance/potiposition transducer

2905005

<https://www.phoenixcontact.com/in/products/2905005>



Configurable potiposition transducer with plug-in connection technology for connecting potentiometers from 0  $\Omega$  ... 100  $\Omega$  to 0 k $\Omega$  ... 100 k $\Omega$ . Configurable via DIP switch or software. Screw connection technology, order configuration

---

## MINI MCR-2-NAM-2RO-PT - Isolation switch amplifier

2902005

<https://www.phoenixcontact.com/in/products/2902005>



Configurable NAMUR isolation amplifier with plug-in connection technology for proximity sensors, floating switch contacts, and switch contacts with resistance circuit. 2 transistor outputs. Configurable via DIP switch. Push-in connection technology.

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## MINI MCR-2-NAM-2RO - Isolation switch amplifier

2902004

<https://www.phoenixcontact.com/in/products/2902004>



Configurable NAMUR isolation amplifier with plug-in connection technology for proximity sensors, floating switch contacts, and switch contacts with resistance circuit. 2 transistor outputs, configurable via DIP switch. Screw connection technology.

---

## MINI MCR-2-F-UI - Frequency measuring transducer

2902056

<https://www.phoenixcontact.com/in/products/2902056>



Universally configurable frequency transducer for converting frequency (Hz/rpm) and PWM signals into standard signals. Sensor voltages greater than 8.2 V DC are possible in combination with MINI MCR-2-SPS 1033202. Screw connection technology.

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## MINI MCR-2-F-UI-PT - Frequency measuring transducer

2902058

<https://www.phoenixcontact.com/in/products/2902058>




Universally configurable frequency transducer for converting frequency (Hz/rpm) and PWM signals into standard signals. Sensor voltages greater than 8.2 V DC are possible in combination with MINI MCR-2-SPS-PT 1033201. Push-in connection technology.

---

## ME 6,2 TBUS-2 1,5/5-ST-3,81 GY - DIN rail bus connectors

2695439

<https://www.phoenixcontact.com/in/products/2695439>



DIN rail connector (TBUS), 5-pos., for bridging the supply voltage, can be snapped onto NS 35/... DIN rail in accordance with EN 60715

## MINI MCR-2-V8-PB-DP - Communication module

2905636

<https://www.phoenixcontact.com/in/products/2905636>



## IFS-USB-PROG-ADAPTER - Programming adapter

2811271

<https://www.phoenixcontact.com/in/products/2811271>




Programming adapter with USB interface, for programming with software. The USB driver is included in the software solutions for the products to be programmed, such as measuring transducers or motor managers.

---

## ME 6,2 TBUS-2 1,5/5-ST-3,81 GN - DIN rail bus connectors

2869728

<https://www.phoenixcontact.com/in/products/2869728>



DIN rail connector for DIN rail mounting. Universal for TBUS housing. Gold-plated contacts, 5-pos.

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## IFS-BT-PROG-ADAPTER - Adapter

2905872

<https://www.phoenixcontact.com/in/products/2905872>



Bluetooth adapter with micro USB and S-PORT interface for wireless communication with the MINI Analog, MINI Analog Pro, MACX Analog, Interface System Gateways, and PLC logic device series.

---

## TWN4 MIFARE NFC USB ADAPTER - Programming adapter

2909681

<https://www.phoenixcontact.com/in/products/2909681>



Near Field Communication (NFC) programming adapter with USB interface for the wireless configuration of NFC-capable products from Phoenix Contact with software. A separate USB driver is not required.

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## UCT-EM (30X5) - Marker for end clamp

0801505

<https://www.phoenixcontact.com/in/products/0801505>



Marker for end clamp, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: latching, Number of individual labels: 24, text field height: 5 mm, text field width: 30 mm

---

## UCT-EM (30X5) CUS - Marker for end clamp

0801589

<https://www.phoenixcontact.com/in/products/0801589>



Marker for end clamp, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snapped into marker carrier, Number of individual labels: 24, text field height: 5 mm, text field width: 30 mm

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## SK 5,0 WH:REEL - Marker strip

0805221

<https://www.phoenixcontact.com/in/products/0805221>



Marker strip, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 10, text field height: 5 mm, text field width: 90000 mm

---

## UC-EMLP (15X5) - Plastic label

0819301

<https://www.phoenixcontact.com/in/products/0819301>



Plastic label, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 10, text field height: 5 mm, text field width: 15 mm

# MINI MCR-2-V8-PB-DP - Communication module




2905636

<https://www.phoenixcontact.com/in/products/2905636>

## UC-EMLP (15X5) YE - Plastic label

0822615

<https://www.phoenixcontact.com/in/products/0822615>



Plastic label, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 10, text field height: 5 mm, text field width: 15 mm

---

## UC-EMLP (15X5) CUS - Plastic label

0824550

<https://www.phoenixcontact.com/in/products/0824550>



Plastic label, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: adhesive, text field height: 5 mm, text field width: 15 mm

# MINI MCR-2-V8-PB-DP - Communication module




2905636

<https://www.phoenixcontact.com/in/products/2905636>

## UC-EMLP (15X5) YE CUS - Plastic label

0824551

<https://www.phoenixcontact.com/in/products/0824551>



Plastic label, can be ordered: by sheet, yellow, labeled according to customer specifications, mounting type: adhesive, text field height: 5 mm, text field width: 15 mm

---

## UC-EMLP (15X5) SR - Plastic label

0828095

<https://www.phoenixcontact.com/in/products/0828095>



Plastic label, Sheet, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 10, text field height: 5 mm, text field width: 15 mm

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## UC-EMLP (15X5) SR CUS - Plastic label

0828099

<https://www.phoenixcontact.com/in/products/0828099>



Plastic label, can be ordered: by sheet, silver, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 10, text field height: 5 mm, text field width: 15 mm

---

## US-EMLP (15X5) - Plastic label

0828790

<https://www.phoenixcontact.com/in/products/0828790>



Plastic label, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, Number of individual labels: 189, text field height: 5 mm, text field width: 15 mm

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## US-EMLP (15X5) YE - Plastic label

0828873

<https://www.phoenixcontact.com/in/products/0828873>



Plastic label, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, Number of individual labels: 189, text field height: 5 mm, text field width: 15 mm

---

## US-EMLP (15X5) SR - Plastic label

0828874

<https://www.phoenixcontact.com/in/products/0828874>



Plastic label, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, Number of individual labels: 189, text field height: 5 mm, text field width: 15 mm

# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## US-EMLP (15X5) CUS - Plastic label

0830076

<https://www.phoenixcontact.com/in/products/0830076>

Plastic label, Card, can be ordered: by card, white, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 189, text field height: 5 mm, text field width: 15 mm



---

## US-EMLP (15X5) YE CUS - Plastic label

0830077

<https://www.phoenixcontact.com/in/products/0830077>

Plastic label, Card, can be ordered: by card, yellow, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 189, text field height: 5 mm, text field width: 15 mm



# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## US-EMLP (15X5) SR CUS - Plastic label

0830078

<https://www.phoenixcontact.com/in/products/0830078>

Plastic label, Card, can be ordered: by card, silver, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 189, text field height: 5 mm, text field width: 15 mm



---

## UCT-EM (30X5) YE - Marker for end clamp

0830340

<https://www.phoenixcontact.com/in/products/0830340>

Marker for end clamp, Sheet, yellow, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: latching, Number of individual labels: 24, text field height: 5 mm, text field width: 30 mm



# MINI MCR-2-V8-PB-DP - Communication module



2905636

<https://www.phoenixcontact.com/in/products/2905636>

## UCT-EM (30X5) YE CUS - Marker for end clamp

0830348

<https://www.phoenixcontact.com/in/products/0830348>



Marker for end clamp, can be ordered: by sheet, yellow, labeled according to customer specifications, mounting type: snapped into marker carrier, Number of individual labels: 24, text field height: 5 mm, text field width: 30 mm

---

## SZS 0,6X3,5 - Screwdriver

1205053

<https://www.phoenixcontact.com/in/products/1205053>



Actuation tool, for ST terminal blocks, insulated, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)