

Eaton 189822

Catalog Number: 189822

Eaton Moeller series NZM - Molded Case Circuit Breaker. Power supply module for NZM2, 24 VDC



General specifications

Product Name	Catalog Number
Eaton Moeller series NZM electronic accessory	189822
	EAN
	4015081878178
Product Length/Depth	Product Height
76 mm	65 mm
Product Width	Product Weight
68 mm	0.021 kg
Compliances	
IEC	
UL/CSA	
RoHS conform	

Product specifications

Used with

NZM2(-4)-VX(MX)...

Type

Accessory Power supply module

Special features

24 V DC supply to the electronic trip. Mechanical pass-through of the switch's status (I, O) for use by the remote operator.

Voltage rating

24 V DC

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_NZM2](#)

Installation instructions

[eaton-circuit-breaker-interface-module-nzm-xbsm-il012102zu.pdf](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Frame

NZM2

Accessory/spare part type

Other

Power supply module

Accessory

Connection type

Screw terminal (supply connection, rated control voltage)

With push in terminal

With bolt connection

Current consumption - max

100 mA

Strip length

5 mm (supply connection)

Degree of protection

Installation in the switch

Terminal capacity (stranded cable)

0.25 mm² - 0.75 mm² (1x) at supply connection (insulated ferrule according to DIN46224 / 4)

24 - 16 AWG (1x) at supply connection

0.2 mm² - 1.5 mm² (1x) at supply connection

0.25 mm² - 0.75 mm² (1x) at supply connection (uninsulated ferrule according to DIN46224 / 1)

Terminal capacity (solid cable)

0.2 mm² - 1.5 mm² (1x) at supply connection

Tightening torque

≥ 0.22 Nm

≤ 0.25 Nm

Control voltage tolerance

+/- 20%



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia