



Connectors > RF Connectors > Coax Connectors



RF Interface: **UHF**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **15.5 mm [.61 in]**

Impedance: **50 Ω**

RF Connector Coupling Mechanism: **Threaded**

Features

Product Type Features

RF Interface	UHF
RF Connector Style	Jack
Connector System	Cable-to-Panel
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Cable Connector Orientation	Straight
Body Material	Zinc
Body Plating Material	Nickel

Contact Features

RF Connector Center Contact Plating Material	Tin (Sn)
RF Connector Center Contact Material	Brass

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------



Mechanical Attachment

Panel Mount Feature Type	Flange
RF Connector Coupling Mechanism	Threaded
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Solder
Detent	Without

Dimensions

RF Connector Mated Outer Diameter (Approximate)	15.5 mm[.61 in]
---	-----------------

Packaging Features

Packaging Method	Package
------------------	---------

Other

Dielectric Material	PBT
---------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (3.1% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #CAT-Z35-GPPRM
SCHRACK SNR Slimline Relay Package

TE Part #1658622-3
16 NOVO MIL/CTR 30DP, LEAD FREE

TE Part #2176185-7
CRGH0805 1% 1K2 0.33W

TE Part #1658621-3
16 NOVO MIL/CTR 15DP, LEAD FREE

TE Part #3-640441-4
04P MTA100 CONN ASSY WHT

TE Part #2-1393763-8
V23100V4312C000

TE Part #1658622-6
26 NOVO MIL/CTR 30DP, LEAD FREE

TE Part #6-2176216-0
CPF A 0603 91K 0.1% 25PPM 1K RL

TE Part #1-1393586-4
V23535A2200A162=BKMOD421
HEADE

Documents

Product Drawings
UHF Pnl Skt 4H Nickel Pltd
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5-1814816-1_B.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_5-1814816-1_B.3d_igs.zip
English



Customer View Model

[ENG_CVM_CVM_5-1814816-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Economy RF Coaxial Connectors](#)

English

[Product Specification](#)

English