

M18 FBS127DO-OC

M18 FUEL™ DUAL-TRIGGER DEEP CUT BAND SAW WITH ONE-KEY™

- Dual trigger activation, requires the user to have always both hands on the tool and automatically shuts down the tool whenever one hand is taken off
- Maximum control for any material, 4-step speed mode & variable speed trigger; ideal for working with stainless steel and aluminium
- ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools. ONE-KEY™ also features a remote locking functionality
- Cut-stop technology, the tool shuts off automatically after the cut for increased user safety
- Large cutting capacity up to 127 x 127 mm material diameter
- Integrated blade cover protects user from injuries by preventing any access to the blade
- Second trigger included in the top handle
- Tool-free blade locking mechanism for quick and easy saw blade changes
- Lockable adjustable shoe
- Solid metal rafter hook for quick and easy job site storage
- Slim full metal motor housing design and LED work surface illumination for best cut visibility
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability



REDLITHIUM™

No load speed (m/min)	0 – 168
Cutting capacity rect. stock (mm)	127 x 127
Blade length (mm)	1139.8
Weight with battery pack (EPTA) (kg)	5.8 (M18 B5)
Kit included	No batteries supplied, No charger supplied, Kitbox
Article Number	4933498311

