

Basic 250-24 W (601533000) Compressor Basic

(220-240 V / 50 Hz); Cardboard box

- Powerful, robust compressor for simple, commercial use
- Oil-lubricated piston condenser
- For single phase alternating current
- Working pressure can be regulated according to application by means of pressure reducer with manometer
- Good cold start feature thanks to push button with safety valve
- Overload protection: protects the motor from overheating
- Rubberised, stable wheels for mobile use
- Testing not necessary before initial operation
- Additional manometer for displaying the tank pressure
- Rubber-coated handle for comfortable handling
- 10 years tank warranty against rusting

[Link to Product](#)

Illustration



Product may differ from Image

System Application Images



Characteristics

Suction rate	200 l/min / 53 gal/h
Filling capacity	110 CFM / 3.9 cfm
Effective delivery volume (at 80% max. pressure)	95 CFM / 3.4 cfm
Maximum pressure	8 bar / 116 psi
Rated input power	1.5 kW

Maximum speed	2850 RPM
Tank capacity	24 l / 6.3 gal
Sound pressure level (LpA)	97 dB(A)
Dimensions	630 x 406 x 630 mm / 2.1 x 1.4 x 2.1 ft
Weight	27 kg / 59.5 lbs
Cable length	1.5 m / 5 ft

Noise emission

Sound pressure level	97 dB(A)
----------------------	----------