



EN ISO 20345:2011


RESOLUTE
FORZA HIGH
43469-05L
S3 SRC *CI AVAILABLE
Size: 36-48
Weight: 650 gr.

Fit: 11

Working Environment:
 Multipurpose, Logistics and Light Industry, Components and Automotive, ESD Areas


FEATURES

UPPER

 Mesh H.T. no ladder
 MicroFiber Rubber with Scratch
 Bumper 1,8-2,0 mm

LINING

3D Green Air 320 gr.

ANTISLIP LINING

DUALMICRO

INSOLE

Qrs01

TOE CAP

Fiber cap SXT

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Ankle boot

SOLE
PU / PU ESD-PLUS SRC

Double density PU sole, Outer- and in-between sole with ESD compound. For use in contact with sensitive electronic equipment. Light and comfortable, very versatile, highly non-slip SRC Antislip standard.

TECHNOLOGIES

Removable Insole


Anatomical breathable insole. Resistant fabric with recycled open-cell foam that absorbs shocks and reduces fatigue. Eliminates sweat with its high ability to evaporate it. Continuous comfort for months and months of use


Protection elements


Composite toecap with fiberglass. Resistant to over 200J. Non metal perforation resistant insert to over 1100 N with a 3.0 mm truncated cone nail. Protection over the entire sole of the foot. Flexible and comfortable


Lateral stability
dynamic HC control
 technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.


Torsional stability
STABIL•ACTIVE

Support made of rigid plastic material. It supports the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.


Electrical features


ESD footwear discharge static electricity and avoid damaging surrounding objects; they are designed in compliance with the following standards: IEC EN 61340-5-1:2016 - IEC EN 61340-4-3:2018 - IEC EN 61340-4-5:2018.

Other
D30
 PROGRESSIVE CUSHIONING
 AND ADAPTIVE STABILITY

D30 materials are made using a combination of advanced polymer chemistry and cutting-edge science. It absorbs and dissipates energy during and impact, with superior stability, cushioning and anti-fatigue effect.


SRC (SRA+SRB)

 SOLE 43
 PU - PU

SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32	0.39
	HEEL (CONTACT ANGLE °) ≥0.28	0.40
SRB STEEL + GLYCEROL	FLAT ≥0.18	0.24
	HEEL (CONTACT ANGLE °) ≥0.13	0.23

EN ISO 20344:2011