

Vacuum Cleaner LXT®

DCL182

18V • 15,4 kPa • 0.5 l

High-suction vacuum cleaner with two power settings

This silent vacuum cleaner, with high suction power and two power settings, is ideal for removing dirt and dust from the floor, staircases, jobsite or vehicle.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Air volume	1,0 m³/min
Max. sealed suction	54 mbar
Continuous Use 18V / 5.0 Ah Battery	66 / 33 min
Continuous Use 18V / 6.0 Ah Battery	39 min
Tank Capacity for Dust	0,5 L
Sound Pressure Level (L _{pA})	71 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s²
Tool weight with battery	1,3 - 1,6 kg
Product Dimensions (L x W x H):	1004 x 115 x 151 mm
Continuous Use 18V / 3.0 Ah Battery	40 / 20 min
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Suction power	11 / 30 W
Product net weight	1,0 kg

User benefits

- Low noise level for pleasant work.
- Increased storage capacity for longer time between waste disposal
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Optional AC

191496-7
Flexible Hose



191D67-4
Round brush



191D75-5
Cyclone Attachment Set



191M30-1
Brush Nozzle



422437-5
Rubber Crevice Nozzel 330 x Ø35



Other

User manual

Parts drawing