

Product Compliance

For compliance documentation, visit the product page on TE.com>













EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.5% in 27520038520) Decamethylcyclopentasiloxane (D5) (.5% in 27520038520) Octamethylcyclotetrasiloxane (D4) (.5% in 27520038520) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer









This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 <p>TE Part # 638481-1 PLUG, INNER HSG, 2POS KEY A</p>	 <p>TE Part # 1326028-2 0.64MM FEMALE CONTACT, AU, 22AWG</p>	 <p>TE Part # 1326028-3 0.64MM FEMALE CONTACT, AU, 18-20</p>	 <p>TE Part # 638551-3 CONTACT, FEMALE, 0.64MM, SN, 18-20</p>
 <p>TE Part # 1326028-4 0.64MM FEMALE CONTACT, AU, 22AWG</p>	 <p>TE Part # 638551-2 CONTACT, FEMALE, 0.64MM, SN, 22</p>	 <p>TE Part # 638485-1 PLUG OUTER HSG, 2POSN</p>	 <p>TE Part # 638551-4 CONTACT, FEMALE, 0.64MM, SN, 22</p>
 <p>TE Part # 1326028-5 .64MM FEM CONT, AU, 18-20, FORMED</p>	 <p>TE Part # 1326028-6 0.64MM FEMALE CONTACT, AU, 22AWG</p>	 <p>TE Part # 1326028-1 0.64MM FEMALE CONTACT, AU, 18-20</p>	 <p>TE Part # 638551-1 CONTACT, FEMALE, 0.64MM, SN, 18-20</p>

Customers Also Bought

 <p>TE Part #CAT-HST-SCT SCT Heat Shrink Tubing</p>	 <p>TE Part #4-2098541-2 3POS, MCON 1.2 CB REC 2p TL SEALED</p>	 <p>TE Part #1924943-1 PLUG ASSY, 96P GPEC II KEY E RIGHT EXIT</p>	 <p>TE Part #9-2141157-5 SHIELD CRIMP FERRULE, 90DEG</p>
 <p>TE Part #2141156-5 SINGLE WIRE SEAL, 8MM HV, 90DEG</p>	 <p>TE Part #2141155-5 PROTEC. COVER 8MM HV, 90DEG</p>	 <p>TE Part #184315-1 3 POS. PLUG ASSY., KEY B</p>	 <p>TE Part #1217003-1 110 FASTON, REC., 18-14 AWG, BR</p>



Documents

Product Drawings

[0.64MM, 2POSN SEALED PLUG, BLA](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1438426-1_C.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1438426-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1438426-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English