


# SD5800



## Industrial gas counter

SDR14DGXFRKG/US-100



Product characteristics	
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1
Measuring range	0.8...83.4 l/min      0.3...27.6 m/s      0.05...5 m³/h
Process connection	threaded connection G 1/4 internal thread DN8
Application	
Application	for industrial applications
Media	helium
Medium temperature [°C]	-10...60
Min. bursting pressure [bar]	64
Pressure rating	16 bar      1.6 MPa
MAWP (for applications according to CRN) [bar]	9.5
Electrical data	
Operating voltage [V]	18...30 DC; (to SELV/PELV)
Current consumption [mA]	< 80
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	1



## Industrial gas counter

SDR14DGXFRKG/US-100

Inputs / outputs			
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Inputs			
Inputs	counter reset		
Outputs			
Output signal	switching signal; analogue signal; pulse signal; IO-Link; (configurable)		
Electrical design	PNP/NPN		
Number of digital outputs	2		
Output function	normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC [V]	2.5		
Permanent current rating of switching output DC [mA]	150; (per output)		
Number of analogue outputs	1		
Analogue current output [mA]	4...20; (scalable)		
Max. load [ $\Omega$ ]	500		
Pulse output	consumed quantity meter		
Short-circuit protection	yes		
Type of short-circuit protection	pulsed		
Overload protection	yes		
Measuring/setting range			
Measuring range	0.8...83.4 l/min	0.3...27.6 m/s	0.05...5 m <sup>3</sup> /h
Display range	0...100 l/min	0...33.1 m/s	0...6 m <sup>3</sup> /h
Resolution	0.2 l/min	0.1 m/s	0.01 m <sup>3</sup> /h
Set point SP	1.3...83.3 l/min	0.4...27.6 m/s	0.08...5 m <sup>3</sup> /h
Reset point rP	0.9...82.9 l/min	0.3...27.5 m/s	0.05...4.97 m <sup>3</sup> /h
Analogue start point ASP	0...66.6 l/min	0...22.1 m/s	0...4 m <sup>3</sup> /h
Analogue end point AEP	16.7...83.3 l/min	5.5...27.6 m/s	1...5 m <sup>3</sup> /h
Low flow cut-off LFC	0.6...0.8 l/min	0.2...0.3 m/s	0.04...0.05 m <sup>3</sup> /h
In steps of	0.1 l/min	0.1 m/s	0.01 m <sup>3</sup> /h
Pressure monitoring			
Measuring range [bar]	-1...16		
Display range [bar]	-1...20		
Resolution [bar]	0.05		
Set point SP [bar]	-0.92...16		
Reset point rP [bar]	-1...15.92		
Analogue start point [bar]	-1...12.8		
Analogue end point [bar]	2.2...16		
In steps of [bar]	0.01		
Volumetric flow quantity monitoring			
Measuring range	0...100000000 m <sup>3</sup>	0...353146667.2 scf	
Display range	0...100000000 m <sup>3</sup>	0...353146667.2 scf	
Set point SP	0.001...10000000 m <sup>3</sup>	0.05...353146667.2 scf	
Pulse value	0.001...10000000 m <sup>3</sup>	0.05...353146667.2 scf	
In steps of	0.0001 m <sup>3</sup>	0.005 scf	



## Industrial gas counter

SDR14DGXFRKG/US-100

Pulse length	[s]	0.01...2
<b>Temperature monitoring</b>		
Measuring range	-10...60 °C	14...140 °F
Display range	-24...74 °C	-11.2...165.2 °F
Resolution	0.2 °C	0.5 °F
Set point SP	-9.7...60 °C	14.6...140 °F
Reset point rP	-10...59.7 °C	14...139.4 °F
Analogue start point	-10...46 °C	14...114.8 °F
Analogue end point	4...60 °C	39.2...140 °F
In steps of	0.1 °C	0.1 °F
<b>Accuracy / deviations</b>		
Temperature coefficient	[1/K]	± 0,07 % MW
Accuracy (in the measuring range)		± (6 % MW + 0,6 % MEW); at medium temperature 23 °C
Repeatability		0,8 % MW + 0,2 % MEW
<b>Pressure monitoring</b>		
Repeatability		± 0,2
	[% of the final value]	
Characteristics deviation		< ± 0,5; (BFSL = Best Fit Straight Line)
	[% of the final value]	
Greatest TEMPCO of the span		± 0,15
	[% MEW / 10 K]	
Greatest TEMPCO of the zero point		± 0,25
	[% MEW / 10 K]	
<b>Temperature monitoring</b>		
Accuracy	[K]	± 0,5; (medium flow in the limit area of the flow measurement range)
<b>Response times</b>		
Response time	[s]	0.1; (dAP = 0)
Damping process value dAP	[s]	0...5
<b>Pressure monitoring</b>		
Response time	[s]	0.05
<b>Temperature monitoring</b>		
Dynamic response T05 / T09	[s]	T09 = 0,5
<b>Software / programming</b>		
Parameter setting options		hysteresis / window; normally open / normally closed; current/pulse output; display can be rotated and switched off; Display unit; totaliser
<b>Interfaces</b>		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9 CDV
Profiles		Digital Measuring Sensor (0x800A), Identification and Diagnosis (0x4000)
SIO mode		yes
Required master port type		A

# SD5800



## Industrial gas counter

SDR14DGXFRKG/US-100

Process data analogue	8	
Process data binary	2	
Min. process cycle time [ms]	7.2	
Supported DeviceIDs	<b>Type of operation</b> default	<b>DeviceID</b> 1301

Operating conditions		
Ambient temperature [°C]		0...60
Storage temperature [°C]		-20...85
Max. relative air humidity [%]		90
Protection		IP 65; IP 67

Tests / approvals		
EMC	DIN EN 60947-5-9	
CPA approval	model number	003TG
	accuracy class	-
	maximum allowable error	± 7 % FS
	Q (min)	0,05 m <sup>3</sup> /h (He)
	Q (t)	-
	Q (max)	5 m <sup>3</sup> /h (He)
Vibration resistance	DIN EN 68000-2-6	5 g (10...2000 Hz)
MTTF [years]		180
UL approval	UL Approval no.	I012
	File number UL	E174189
Pressure Equipment Directive	Sound engineering practice; can be used for stable gases fluid group 2	

Mechanical data		
Weight [g]		554
Housing		rectangular
Dimensions [mm]		182 x 45.4 x 67.8
Materials	PBT+PC-GF30; PPS GF40; stainless steel (304/1.4301); stainless steel (303/1.4305); steel (1.5523) galvanised; 2.0401 (brass / CW614N); FKM	
Materials (wetted parts)	EN AW-6082 (aluminium); stainless steel (303/1.4305); FKM; ceramics glass passivated; PPS GF40; Al <sub>2</sub> O <sub>3</sub> (ceramics); acrylate	
Process connection	threaded connection G 1/4 internal thread DN8	

Displays / operating elements		
Display		colour display 1,44", 128 x 128 pixels
		2 x LED, yellow

Remarks		
Remarks		MW = measured value
		MEW = Final value of the measuring range
		Standard conditions: 1013.25 mbar / 15 °C / 0 % relative humidity
		For information about installation and operation please see the operating instructions.
Pack quantity		1 pcs.

# SD5800



## Industrial gas counter


SDR14DGXFRKG/US-100

### Electrical connection

Connector: 1 x M12; coding: A



### Connection



OUT1/IO-Link: switching output flow  
switching output temperature  
switching output pressure  
Pulse output quantity meter

OUT2/InD: signal output Preset counter  
switching output flow  
switching output temperature  
switching output pressure  
analogue output flow  
analogue output temperature  
analogue output pressure  
signal output Preset counter  
Pulse output quantity meter  
input counter reset