


CamCleaner 300 Concealed



Advantages

- Healthier employees
- Less cleaning
- Lower energy costs
- Reduced environmental impact
- Clean products, fewer operational disruptions
- Easy to adapt ducts and diffusors
- Less odour

Applications: Air purifier for rooms measuring up to 100 m², for example small or medium offices. Can also be used to complement larger air purifiers.

Nominal voltage range: 200..240V

Filter: F7 and E11

Duct Connection: 2 pc Ø250mm

Capacity: 316 m³/h

Installation: Wall or ceiling (built in)

Design: Galvanized sheet steel

Air purification area: MAX 100m²

Item no.	Type	Dimensions (WxHxD) mm	Weight kg	Air volume m ³ /h	Initial pressure drop Pa	Noise level dBa	Power output W	Filter included in standard version *
94000011	CamCleaner 300 Concealed	1052X316X364	21,4	316	137		28	XLT F7 + E11

Upgrades / Accessories / Exchange

Art. Nr	Description
Upgrades	
94000012	Upgrade with standard MiniCarb (CEX003/A1) and 97mm Ecopleat
94000013	Upgrade with MiniCarb for Formaldehyde (CEX004/J2) and 97mm Ecopleat
94000014	Upgrade to H13
Accessories	
94000015	UK plug
Exchange	
	HI-FLO XLT 7 D50+ HFGX-F7-287/287/370-5-25
	MICRETAIN TRE 11-287X287X292-01
	ECOPLEAT ECO 3GPF 287X287X97-M5
	MEGAFLO MFE 13-287X287X292-01/10
	MINICARB MINICARB/CEX003/A1 d=90/80 mm L=250
	MINICARB MINICARB/CEX004/J2 d=90/80 mm L=250

As part of our program for continuous improvement, Camfil reserves the right to change specifications without notice. 2015-05-30