

745781-4

✓ ACTIVE

AMPLIMITE | AMPLIMITE HD-20

TE Internal #: 745781-4

9 Position D-Shaped Connector, Receptacle, Board-to-Board,
 Board Mount, 1 Shell Size, 2.74 mm [.108 in] Centerline, AMPLIMITE
 HD-20

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Receptacle Assembly: Right Angle, Shell Size 1, 2.74mm



Number of Positions: **9**

Connector & Housing Type: **Receptacle**

Connector System: **Board-to-Board**

Connector Mounting Type: **Board Mount**

Connector Shell Size: **1**

[All D-Sub Receptacle Assembly: Right Angle, Shell Size 1, 2.74mm \(64\)](#)

Features

Product Type Features

Ground Feature Type	Grounding Straps
Shell Material Configuration	Front Metal Shell
Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Connector Shell Size	1
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	9
Number of Rows	2
PCB Mount Orientation	Right Angle

Body Features

Insert Material	Zinc
-----------------	------

Shell Plating Material	Tin
Mating Retention Feature Material	Zinc
Primary Product Color	Black
Connector Profile	Standard

Contact Features

	30 μ in
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
Contact Shape & Form	Round
Contact Current Rating (Max)	6 A
Contact Options	Installed

Termination Features

Termination Post & Tail Diameter	.66 mm [.026 in]
Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.18 mm [.125 in]

Mechanical Attachment

Mating Retention Feature Plating Material	Clear Chromate
Mounting Feature Plating Material	Tin
Mounting Feature Material	Brass
Mounting Hole Diameter	3.18 mm [.125 in]
Connector Mounting Type	Board Mount
PCB Mount Retention	With
PCB Mount Retention Type	Mounting Hole
Mating Retention	With
Mating Retention Type	Threaded Insert, 4-40 UNC

Housing Features

Housing Material	Thermoplastic
Shell Material	Steel
Centerline (Pitch)	2.74 mm [.108 in]

Dimensions

PCB Thickness (Recommended)	2.36 mm [.093 in]
-----------------------------	-------------------

Row-to-Row Spacing 2.84 mm [.112 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Compatible With Approved Standards Products	UL E28476
---	-----------

Packaging Features

Packaging Quantity	130
--------------------	-----

Packaging Method	Tray
------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM7-H3
 IDC D-Sub: Plug Assembly, Low Profile, Signal, 2.77 mm




TE Part # CAT-AM7-248H3
 IDC D-Sub: Plug Assembly, Wire to Wire, Signal, 2.77 mm



TE Part # 1-747944-5
 09 SHLDG ENCL PLUG,LEAD FREE

Also in the Series | AMPLIMITE HD-20



D-Shaped Connectors(285)



PCB D-Sub Connectors(285)

Customers Also Bought



TE Part #839686-E
 IDCCS SRC 1,27 6 * SFX APU 160 PVC



TE Part #04-1106-5001
 PT5A-100-N34-FR-5K-C25



TE Part #1-84953-6
 1MM FPC HORZ.TOP CONT.ASSY 16P



TE Part #2301994-7
 RJ45 JACK INT.MAG. 1GB 1X1



TE Part #5228686-1
 TWIN BNC PCB RCPT



TE Part #1-5499786-2
 A/L UNIV HDR 64P RA LAT



TE Part #5535089-5
 ASSEMBLY,RECEPTACLE,EUROCARD, T



TE Part #5650933-5
 ASSY,PIN,EUROCARD,TYPE R,LEAD-T



Documents

Product Drawings

[09 MSFL RCPT RA 318 \(IN,FM\)](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_745781-4_AH.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_745781-4_AH.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_745781-4_AH.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English