

318.3243

CONNECTOR
32A 2P+E 6h 200-250V 60Hz 50Hz
Screw terminals



* Product image may be indicative



EN IEC 60309-1 (2022)
EN IEC 60309-2 (2022)
Low voltage direct. 2014/35/EU

GENERAL CHARACTERISTICS

Commercial Series	OPTIMA Series
Synthetical description	CONNECTOR
Description	
The OPTIMA Series connector is designed for demanding electrical industrial environments, featuring a rated voltage of 200-250V and a rated current of 32A. This 2P+E connector operates at both 50Hz and 60Hz frequencies, with a 6h hour position. It offers superior protection with IP66/IP67/IP69 ratings, ensuring excellent resistance to dust and water ingress. Equipped with screw terminals, it facilitates secure and efficient connections. Available in a straight outlet type, the connector can also be ordered in black by appending “.K” to the catalogue number. This robust connector is engineered to meet the rigorous demands of industrial settings, ensuring durability and reliability.	
Mounting version	PORTABLE

TECHNICAL CHARACTERISTICS

Rated current	32A
Poles	2P+E
Hour position	6h
Rated voltage	200-250V
Working frequency	60Hz
	50Hz
Terminals	Screw terminals

PHYSICAL CHARACTERISTICS

Mounting version	PORTABLE
Colour	BLUE
Material	THERMOPLASTIC
Protection degree	Watertight
Protection degree IP	IP66/IP67/IP69
Protection degree IK	IK08
Types of available outlets	STRAIGHT
Contact material	CuZn (brass)
Cable entry	CABLE GLAND

DOWNLOAD

Technical drawing [PDF]
Technical drawing [STP]
Technical drawing [DWG]

OPTIONS & VARIOUS NOTES

Catalogue notes	Version also available in black; just add “.K” at the end of the catalogue number.
-----------------	--