



Type A casting only
 Type C with plain blind bore, Tol. H7

Type D with threaded through bore
 Type E with threaded blind bore

d1	d2 Thread Type E	Type D Type E	d3 H7 Bore (B) Type C	d4 -0,5	h1 -1	h2 ≈	t1 min.	t2
40	M 6	M 8	B 8	15	25	12,5	15	15
50	M 8	M 10	B 10	19	32	16	18	20
60	M 10	M 12	B 12	21	40	20	22	26
70	M 12	M 16	B 16	26	46	23	28	32

Specification

Aluminum

matt (MT)

tumbled

polished (PL)

domed head additionally

highly polished

Information

Hand knobs GN 5336 are forged, therefore a close grain structure is maintained providing a high tensile strength and a smooth surface.

Possible casting flash is invisible due to the applied advantageous production techniques.

How to order

Hand knob
GN 5336-50-M10-E-MT

Code Nr.	d1	d2 (d3)	Type	Finish