




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **2**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector System	Wire-to-Board, Wire-to-Wire
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Blue
-----------------------	------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

--



Mating Alignment Type	Polarization
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Centerline (Pitch)	15.11 mm[.595 in]

Dimensions

	.475 in
--	---------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part









numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 1217092-1 PL 250 TERMINAL RECEPTACLE 16-12 AWG BR	 TE Part # 63854-1 250 PL MKIII REC. 18-14AWG BR	 TE Part # 368612-2 POSITIVE LOCK 250 TERMINAL-FLAG	 TE Part # 2-521120-1 HSG RECPT POSILOK MK III 250 Blue
 TE Part # 63933-2 250 PL MKIII REC. 22-18AWG TPBR	 TE Part # 63854-2 250 PL MKIII REC. 18-14AWG TPBR	 TE Part # 1217092-2 PL 250 TERMINAL REC 16-12 AWG TPBR	 TE Part # 63933-1 PL .250 TERMINAL REC 22-18 AWG BR

Also in the Series | Mark II

 Automotive Connector Locks & Position Assurance(1)	 Automotive Housings(6)	 Automotive Terminals(1)	 Connector Seals & Cavity Plugs(1)
 Crimp Terminal Housings(177)	 Insertion & Extraction Tools(3)	 Quick Disconnects(173)	

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(177)



Insertion & Extraction Tools(3)



Insulation Boots & Sleeves(5)




Quick Disconnects(173)

Customers Also Bought



TE Part #1-1375820-3
CST-100 II HOUSING 13 POS



TE Part #2-520083-2
ULTRA-FAST .110/.125 ASY REC 22-18 TPBR



TE Part #521011-1
ULTRA-POD 250 ASSY REC 18-14 AWG NPST



TE Part #521600-2
ULTRA-POD 187 ASY REC 22-18 AWG TPBR



TE Part #CAT-P87074-C1701A
POWER TRIPLE LOCK High Temperature Caps



TE Part #170324-1
187 PL MKII REC. 24-20AWG PTBR



TE Part #5-1971876-7
PTL 3X5 PLUG HSG HIGH TEMP KEY A LGR



TE Part #CAT-UL8-187021
ULTRA POD: Straight, Receptacle Assembly, Tin Plated, .187 inch

Documents

Product Drawings
PL 250 HOUSING REC BLUE 6/6 NYLON V2

English

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_1-520935-5_AW.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-520935-5_AW.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-520935-5_AW.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON Housings](#)

English

[Positive Lock Receptacles](#)

English

Agency Approvals

[UL Report](#)

English

[UL Report](#)

English

[UL Report](#)

English