



The Product

- Robust workshop lamp. Resistant to being run over by small cars.
- Non-flicker light that doesn't tire the eyes.
- Lights in cold weather.
- Resistant to oil, petrol etc.
- No fire hazard due to low operation temperature
- Will not roll on inclined surfaces.
- Both water and dust tight.
- Suitable for both indoor and outdoor use.



Specifications

Lumen	900
Durability	IP65 (dust tight / protected against water jets)
Length (incl. hook)	455mm
Weight	775g
Cable	5m H05RN-F, European flat plug
Pcs per box	10
Product code	19E011

Accessories and spare parts

Product code	Description
14203	Magnetic holder
19E084	Fluorescent tube, 11 watt / 4-pin
19E323	Top cap with hook
19E327	Reflector
19E331	Tube shield
19E338	Handle
19E380	Electronic circuit board 230 volt