

UCT-WMS 4,7 (12X5,5) OG - Wire marking tag



0830210
<https://www.phoenixcontact.com/gb/products/0830210>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, Sheet, orange, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, BLUEMARK E.CARD, THERMOMARK PRIME 2.0, cable diameter range: 2.5 ... 4.7 mm, mounting type: slide-on, for terminal block width: 5.2 mm, Number of individual labels: 45, text field height: 5.5 mm, text field width: 12 mm

Your advantages

- The UCT-WMS ... UniCard labeling range includes markers that can be threaded onto conductors
- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and precisely using the THERMOMARK CARD and the BLUEMARK LED
- The sheets provide space for including function texts
- The markers support multi-line labeling
- The format automatically ensures printing with a high degree of positioning accuracy

Commercial data

Item number	0830210
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	BG2218
Product key	BG2218
GTIN	4046356629799
Weight per piece (including packing)	16.275 g
Weight per piece (excluding packing)	12 g
Customs tariff number	39269097
Country of origin	PL

UCT-WMS 4,7 (12X5,5) OG - Wire marking tag



0830210

<https://www.phoenixcontact.com/gb/products/0830210>

Technical data

Notes

General	Can be labeled via thermal transfer
---------	-------------------------------------

Product properties

Product type	Conductor marking
Pitch	5.2 mm
Type	Card form

Marking

Number of individual labels	45
Number of individual labels per row	9
Identification technology	Thermal transfer for sheets and cards

Dimensions

Width	5.5 mm
Height	7.1 mm
Length	12 mm
Pitch	5.2 mm

External dimensions

Outside diameter	2.5 mm ... 4.7 mm
------------------	-------------------

Text field

Text field width	12 mm
Text field height	5.5 mm

Material specifications

Color	orange (RAL 2003)
Material	PC
Flammability rating according to UL 94	V0
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone and halogen

Cable/line

External cable diameter	2.5 mm ... 4.7 mm
-------------------------	-------------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

UCT-WMS 4,7 (12X5,5) OG - Wire marking tag



0830210

<https://www.phoenixcontact.com/gb/products/0830210>

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesa film test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
---------------	---------------------------

UCT-WMS 4,7 (12X5,5) OG - Wire marking tag



0830210

<https://www.phoenixcontact.com/gb/products/0830210>

Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Standards

Standards/regulations	EN 45545-2
-----------------------	------------

Mounting

Mounting type	slide-on
---------------	----------

UCT-WMS 4,7 (12X5,5) OG - Wire marking tag



0830210

<https://www.phoenixcontact.com/gb/products/0830210>

Classifications

ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UCT-WMS 4,7 (12X5,5) OG - Wire marking tag



0830210

<https://www.phoenixcontact.com/gb/products/0830210>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk