



## SAFETY DATA SHEET CLEAR MECHANICAL OIL Aerosol

### 1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

**PRODUCT NAME** CLEAR MECHANICAL OIL Aerosol

**PRODUCT NO.** CMO200D [ECMO200D]

**APPLICATION** Lubricant

**SUPPLIER** ELECTROLUBE. A division of  
HK WENTWORTH LTD  
KINGSBURY PARK, MIDLAND  
ROAD  
SWADLINCOTE  
DERBYSHIRE, DE11 0AN  
UNITED KINGDOM  
+44(0)1283 222 111  
+44(0)1283 550 177  
info@hkw.co.uk

Supplied by:  
**RS Components Ltd,**  
Birchington Road, Corby, Northants, NN17 9RS.  
Tel: +44 (0) 1536 402888 (8am to 8pm)  
Email: technical.help@rs-components.com

**EMERGENCY TELEPHONE** +44(0)1283 222 111 between 8.30 am - 5.00pm Mon - Fri

### 2 HAZARDS IDENTIFICATION

Extremely flammable.

Repeated exposure may cause skin dryness or cracking.

Vapours may cause drowsiness and dizziness.

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

**CLASSIFICATION** F+;R12. N;R51/53. R66, R67.

#### ENVIRONMENT

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point. Dispose of waste and residues in accordance with local authority requirements.

#### PHYSICAL AND CHEMICAL HAZARDS

Aerosol containers can explode when heated, due to excessive pressure build-up. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited.

### 3 COMPOSITION/INFORMATION ON INGREDIENTS

| Name        | EC No.    | CAS-No.  | Content | Classification                 |
|-------------|-----------|----------|---------|--------------------------------|
| PENTANE     | 203-692-4 | 109-66-0 | 30-60%  | F+;R12 Xn;R65 R66 R67 N;R51/53 |
| PROPAN-2-OL | 200-661-7 | 67-63-0  | 1-5%    | F;R11 Xi;R36 R67               |

The Full Text for all R-Phrases are Displayed in Section 16

#### COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

### 4 FIRST-AID MEASURES

#### NOTES TO THE PHYSICIAN

Treat symptomatically

#### INHALATION

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention. Get medical attention.

#### INGESTION

Immediately rinse mouth and provide fresh air.

## CLEAR MECHANICAL OIL Aerosol

### SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

### EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

## 5 FIRE-FIGHTING MEASURES

### EXTINGUISHING MEDIA

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

### SPECIAL FIRE FIGHTING PROCEDURES

Move container from fire area if it can be done without risk.

### UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

## 6 ACCIDENTAL RELEASE MEASURES

### SPILL CLEAN UP METHODS

Absorb in vermiculite, dry sand or earth and place into containers. Ventilate well.

## 7 HANDLING AND STORAGE

### USAGE PRECAUTIONS

Avoid spilling, skin and eye contact. Provide good ventilation.

### STORAGE PRECAUTIONS

Store at moderate temperatures in dry, well ventilated area.

## 8 EXPOSURE CONTROLS/PERSONAL PROTECTION

| Name        | Std | TWA - 8 hrs |            | STEL - 15 min |            | Notes |
|-------------|-----|-------------|------------|---------------|------------|-------|
| PENTANE     | WEL | 600 ppm     | 1800 mg/m3 |               |            |       |
| PROPAN-2-OL | WEL | 400 ppm     | 999 mg/m3  | 500 ppm       | 1250 mg/m3 |       |

WEL = Workplace Exposure Limit.

### OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

### HYGIENE MEASURES

Wash at the end of each work shift and before eating, smoking and using the toilet. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke. DO NOT SMOKE IN WORK AREA!

## 9 PHYSICAL AND CHEMICAL PROPERTIES

|                                |                                                  |                               |                                 |
|--------------------------------|--------------------------------------------------|-------------------------------|---------------------------------|
| APPEARANCE                     | Aerosol Liquid                                   |                               |                                 |
| COLOUR                         | Colourless                                       |                               |                                 |
| ODOUR                          | Characteristic                                   |                               |                                 |
| PHYSICAL DATA COMMENTS         | Information given concerns the major ingredient. |                               |                                 |
| VOLATILITY DESCRIPTION         | Volatile.                                        |                               |                                 |
| SOLUBILITY                     | Immiscible with water                            |                               |                                 |
| BOILING POINT (°C)             | 36 (96.8 F)                                      | MELTING POINT (°C)            | -130 (-202 F)                   |
| RELATIVE DENSITY               | 0.650 @ 20 °c (68 F)                             | BULK DENSITY                  | 650 kg/m3                       |
| VAPOUR PRESSURE                | 5.33 kPa @ 19 °c (66.2 F)                        | FLASH POINT (°C)              | - 48 (-54.4 F) CC (Closed cup). |
| AUTO IGNITION TEMPERATURE (°C) | 309 (588.2 F)                                    | FLAMMABILITY LIMIT - LOWER(%) | 1.4                             |
| FLAMMABILITY LIMIT - UPPER(%)  | 7.8                                              |                               |                                 |

## 10 STABILITY AND REACTIVITY

## CLEAR MECHANICAL OIL Aerosol

### STABILITY

Stable under normal temperature conditions.

### CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with acids and alkalies.

## 11 TOXICOLOGICAL INFORMATION

### INHALATION

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. High concentrations of vapours may irritate respiratory system and lead to headache, fatigue, nausea and vomiting.

### SKIN CONTACT

Product has a defatting effect on skin. Prolonged contact may cause dryness of the skin. Prolonged or repeated exposure may cause severe irritation.

### EYE CONTACT

Irritating to eyes.

### OTHER HEALTH EFFECTS

This substance has no evidence of carcinogenic properties.

### ROUTE OF ENTRY

Inhalation.

|                      |                                          |
|----------------------|------------------------------------------|
| Name                 | PENTANE                                  |
| Toxic Dose 1 - LD 50 | >2000 mg/kg (oral rat)                   |
| Toxic Dose 2 - LD 50 | 446 mg/kg (ivn-mouse)                    |
| Toxic Conc. - LC 50  | 364,000 mg/m <sup>3</sup> /30h (inh-rat) |
| Name                 | PROPAN-2-OL                              |
| Toxic Dose 1 - LD 50 | 5045 mg/kg (oral rat)                    |
| Toxic Dose 2 - LD 50 | 3600 mg/kg (oral-mouse)                  |
| Toxic Conc. - LC 50  | 47-73 mg/l/4h (inh-rat)                  |

## 12 ECOLOGICAL INFORMATION

### ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

|                              |             |
|------------------------------|-------------|
| Name                         | PENTANE     |
|                              | PROPAN-2-OL |
| LC 50, 96 Hrs, FISH mg/l     | 9600        |
| EC 50, 48 Hrs, DAPHNIA, mg/l | 10000       |

## 13 DISPOSAL CONSIDERATIONS

### DISPOSAL METHODS

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

## 14 TRANSPORT INFORMATION



|                      |          |
|----------------------|----------|
| UK ROAD CLASS        | 2.1      |
| PROPER SHIPPING NAME | AEROSOLS |
| UN NO. ROAD          | 1950     |
| ADR CLASS NO.        | 2.1      |
| ADR PACK GROUP       | #        |
| ADR LABEL NO.        | 2.1      |
| RID CLASS NO.        | 2.1      |

|                         |                |
|-------------------------|----------------|
| UK ROAD PACK GR.        | #              |
| ADR CLASS               | Class 2: Gases |
| TUNNEL RESTRICTION CODE | (D)            |
| CEPIC TEC(R) NO.        | 20G5F          |
| RID PACK GROUP          | #              |

## CLEAR MECHANICAL OIL Aerosol

|                  |      |              |          |
|------------------|------|--------------|----------|
| UN NO. SEA       | 1950 | IMDG CLASS   | 2.1      |
| IMDG PACK GR.    | #    | EMS          | F-D, S-U |
| MARINE POLLUTANT | No.  | UN NO. AIR   | 1950     |
| AIR CLASS        | 2.1  | AIR PACK GR. | #        |

### 15 REGULATORY INFORMATION

#### SYMBOLS



Extremely Flammable



Dangerous for the environment

#### RISK PHRASES

|        |                                                                                             |
|--------|---------------------------------------------------------------------------------------------|
| R12    | Extremely flammable.                                                                        |
| R51/53 | Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. |
| R66    | Repeated exposure may cause skin dryness or cracking.                                       |
| R67    | Vapours may cause drowsiness and dizziness.                                                 |

#### SAFETY PHRASES

|     |                                                                                                                                       |
|-----|---------------------------------------------------------------------------------------------------------------------------------------|
| A1  | Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. |
| A2  | Do not spray on a naked flame or any incandescent material.                                                                           |
| S2  | Keep out of the reach of children                                                                                                     |
| S16 | Keep away from sources of ignition - No smoking.                                                                                      |
| S23 | Do not breathe vapour/spray.                                                                                                          |
| S37 | Wear suitable gloves.                                                                                                                 |
| S51 | Use only in well-ventilated areas.                                                                                                    |

#### UK REGULATORY REFERENCES

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 1988.

#### ENVIRONMENTAL LISTING

Rivers (Prevention of Pollution) Act 1961. Control of Pollution Act 1974.

#### EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

#### STATUTORY INSTRUMENTS

Control of Substances Hazardous to Health.

#### APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

#### GUIDANCE NOTES

Workplace Exposure Limits EH40.

## CLEAR MECHANICAL OIL Aerosol

### 16 OTHER INFORMATION

#### REVISION COMMENTS

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

#### ISSUED BY

Pawel Zmarzly

#### REVISION DATE

NOVEMBER 2009

#### REV. NO./REPL. SDS

1

#### GENERATED

#### SDS NO.

10337

#### RISK PHRASES IN FULL

|        |                                                                                             |
|--------|---------------------------------------------------------------------------------------------|
| R11    | Highly flammable.                                                                           |
| R12    | Extremely flammable.                                                                        |
| R36    | Irritating to eyes.                                                                         |
| R51/53 | Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. |
| R65    | Harmful: may cause lung damage if swallowed.                                                |
| R66    | Repeated exposure may cause skin dryness or cracking.                                       |
| R67    | Vapours may cause drowsiness and dizziness.                                                 |

#### DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.