

**FAG****6322-M-C3**

Deep groove ball bearing

Deep groove ball bearing 63...-M, single row,
solid brass cage

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	M	Solid brass cage, rolling element guided
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	Without	Bearing not greased
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	110 mm	Bore diameter
D	240 mm	Outside diameter
B	50 mm	Width
C _r	201,000 N	Basic dynamic load rating, radial
C _{0r}	165,000 N	Basic static load rating, radial
C _{ur}	8,800 N	Fatigue load limit, radial
n _G	4,950 1/min	Limiting speed
n _{gr}	4,150 1/min	Reference speed
≈m	11.75 kg	Weight



Mounting dimensions

$d_{a\ min}$	124 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	226 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2.5 mm	Maximum fillet radius

Dimensions

$r_{\ min}$	3 mm	Minimum chamfer dimension
$D_{\ 1}$	197.54 mm	Shoulder diameter outer ring
$d_{\ 1}$	153.26 mm	Shoulder diameter inner ring

Temperature range

$T_{\ min}$	-30 °C	Operating temperature min.
$T_{\ max}$	150 °C	Operating temperature max.

Calculation factors

$f_{\ 0}$	13.8	Calculation factor
-----------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed