

FEATURES

- **Nickel Plated Brass Construction:** Provides durability and corrosion resistance
- **Male Hose Barb Connection:** Ensures a secure fit with 6 mm hoses
- **Female BSPP Threaded Connection:** Compatible with 1/4 inch threaded fittings
- **High Maximum Operating Pressure:** Suitable for applications up to 100 bar
- **Wide Temperature Range:** Operates effectively up to 300 °C

RS PRO 6 mm Hose Barb Hose Connector, 1/4 in BSPP Threaded

RS Stock No: 665-599



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO hose connector is designed for secure and efficient fluid transfer in industrial applications. Featuring a robust nickel-plated brass construction, it offers excellent durability and resistance to corrosion. The connector is ideal for connecting hoses to threaded fittings, ensuring a reliable and leak-free connection.

General Specifications

Connection Gender A	Male
Connection Gender B	Female
Connection Size A	6 mm
Connection Size B	1/4 in
Connection Standard B	BSPP
Connection Type A	Hose Barb
Connection Type B	Threaded
Maximum Operating Pressure	100 bar
Product Type	Hose Connector
Sub Type	Hose Connector

Mechanical Specifications

Body Material	Nickel Plated Brass
Hose Inside Diameter	6 mm

Operation Environment Specifications

Maximum Operating Temperature	300 °C
-------------------------------	--------

Approvals

Standards/Approvals	PED 2014-68-UE, REACH 1907-2006, RoHS 2011-65-CE
---------------------	--

