



### Manual Tensioning Tool for Cable ties with low profile head

- MK10-SB up to 9.5 mm strap width

#### Features and Benefits

- Ideal for easy handling of entire HellermannTyton RPE and PE-Series
- Tensions and cuts off pre-looped cable ties flush at the head



MK10-SB.

TYPE	Strap Width max. (G)	Strap Thickness max.	Weight	Article-No.
MK10-SB	9.5	2.5	0.33 kg	110-10001

All dimensions in mm. Subject to technical changes.

### Manual Tensioning Tool for Cable Ties, simple version


- MK20 up to 4.8 mm strap width
- MK21 up to 7.6 mm strap width

#### Features and Benefits

- Lightweight, ergonomic tools
- For tensioning and cutting HellermannTyton standard cable ties 4.8 - 7.6 mm wide
- MK20 and MK21 ideal for on-site assembly
- Mounted and pre-tensioned ties are cut off by twisting tool



MK20, MK21.



Apply.



Tension.



Twist to cut.

TYPE	Strap Width max. (G)	Strap Thickness max.	Weight	Article-No.
MK20	4.8	1.5	0.05 kg	110-20006
MK21	7.6	2.5	0.05 kg	110-21016

All dimensions in mm. Subject to technical changes.