



0603SFS400F/32-2 Product Details

[Share](#) [Print](#) [Email](#)


0603SFS400F/32-2
(RF0347-000)

TE Internal Number: RF0347-000

 **Active**

Fuses

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Type = DC Slow Blow Fuse
- Surface Mount Construction
- Form Factor (inches) = 0603
- Form Factor (mm) = 1608
- Rated Current = 4 A

[View all Features](#)

Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [CP CATALOG 2011-FUSES](#) (PDF, English)

Product Specifications:

- [0603SFS400F/32-2](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Family Name = SFS

Electrical Characteristics:

- Rated Current (A) = 4
- Cold DCR (Nominal) (Ω) = 0.017
- I^2t (A²sec)² (Nominal) (Ω) = 2.3
- Interrupt Voltage, Max. (VDC) = 32
- Interrupt Current, Max. (A) = 50

Termination Features:

- Construction = Surface Mount

Body Features:

- Type = DC Slow Blow Fuse

Configuration Features:

- Form Factor (inches) = 0603
- Form Factor (mm) = 1608

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- UL Listed = File No. E197536

Environmental:

- Operating Temperature (Max.) (°C) = 125

Conditions for Usage:

- Min Clear Time @ 100% Rated Current (Hr) = 4
- Min Clear Time @ 200% Rated Current (Seconds) = 1
- Min Clear Time @ 300% Rated Current (Seconds) = 0.1
- Min Clear Time @ 800% Rated Current (Seconds) = 0.0005 – 0.001

Other:

- Brand = Raychem

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed



