



I.D. PRO™ Plus SLEEVES

CONTINUED

► PERMASLEEVE™ WIRE MARKING SLEEVES



Heat-Shrink White Polyolefin (B-342)

Part Number	Marker Size Code	Sleeves Per Roll	Range of Wire Dia. Inch (mm)		Approx. Wire Gauge*	Sleeve Dimension Inch (mm)		Maximum Lines of Print ▲	Maximum Characters Across	
			Min.	Max.		A	B		Large	Small
100" Marker Width										
PSIDP-111-125	111	100	.046 (1.17)	.110 (2.79)	22-16	1.00 (25.40)	.235 (6.00)	1	8	11
PSIDP-111-187	111	100	.062 (1.57)	.150 (3.81)	18-12	1.00 (25.40)	.335 (8.50)	1	8	11
PSIDP-211-250	211	100	.094 (2.39)	.215 (5.46)	16-10	1.00 (25.40)	.439 (11.20)	2	8	11
PSIDP-311-375	311	100	.125 (3.18)	.320 (8.13)	12-6	1.00 (25.40)	.645 (16.40)	3	8	11
PSIDP-411-500	411	100	.187 (4.75)	.450 (11.43)	8-1	1.00 (25.40)	.851 (21.60)	4	8	11

▲ I.D. PRO Plus will print up to 8 different lines of text. In wire and strip modes, I.D. PRO Plus will repeat the full legend for the entire length of the label.

*Based on National Electric Code insulation measurement of THHN wire.

Heat-Shrink Yellow Polyolefin (B-342)

Part Number	Marker Size Code	Sleeves Per Roll	Range of Wire Dia. Inch (mm)		Approx. Wire Gauge *	Sleeve Dimension Inch (mm)		Maximum Lines of Print ▲	Maximum Characters Across	
			Min.	Max.		A	B		Large	Small
100" Marker Width										
PSIDP-111-125-Y	111	100	.046 (1.17)	.110 (2.79)	22-16	1.00 (25.40)	.235 (6.00)	1	8	11
PSIDP-111-187-Y	111	100	.062 (1.57)	.150 (3.81)	18-12	1.00 (25.40)	.335 (8.50)	1	8	11
PSIDP-211-250-Y	211	100	.094 (2.39)	.215 (5.46)	16-10	1.00 (25.40)	.439 (11.20)	2	8	11
PSIDP-311-375-Y	311	100	.125 (3.18)	.320 (8.13)	12-6	1.00 (25.40)	.645 (16.40)	3	8	11
PSIDP-411-500-Y	411	100	.187 (4.75)	.450 (11.43)	8-1	1.00 (25.40)	.851 (21.60)	4	8	11

▲ I.D. PRO Plus will print up to 8 different lines of text. In wire and strip modes, I.D. PRO Plus will repeat the full legend for the entire length of the label.

*Based on National Electric Code insulation measurement of THHN wire.