


# Drive shaft adapter DARF-Q13-20

Part number: 8200999

FESTO



## Data sheet

 General operating condition

| Feature                                                   | Value                                                              |
|-----------------------------------------------------------|--------------------------------------------------------------------|
| Size                                                      | 20                                                                 |
| Mounting position                                         | Any                                                                |
| For piston diameter                                       | Ø20                                                                |
| Design                                                    | Drive shaft adapter                                                |
| Symbol                                                    | 00991265                                                           |
| Corrosion resistance class CRC                            | 1 - Low corrosion stress                                           |
| LABS (PWIS) conformity                                    | VDMA24364-C1-L                                                     |
| Suitability for the production of Li-ion batteries        | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 9 according to ISO 14644-1                                   |
| Storage temperature                                       | -20 °C ... 60 °C                                                   |
| Ambient temperature                                       | 0 °C ... 60 °C                                                     |
| Max. bending moment                                       | 5 Nm                                                               |
| Max. axial load static                                    | 350 N                                                              |
| Product weight                                            | 93 g                                                               |
| Type of mounting                                          | Via through-hole and centring sleeve                               |
| Note on materials                                         | RoHS compliant                                                     |
| Drive shaft adapter material                              | Tempered steel                                                     |