

## SMS relay - TC MOBILE I/O X200-4G - 1038567

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



SMS relay and signaling module, European version, monitor analog and digital values via mobile network, switch relay outputs remotely, communication via SMS or mobile network data connection (e-mail transmission, app), supply voltage 10 V ... 60 V DC

### Product Description


The compact electronic alarm annunciator monitors analog and digital values via the mobile network. It also switches relay outputs remotely. The device offers numerous helpful software functions, such as SMS message chain, SMS in event of voltage drop, sending of log books via e-mail, and different user roles. A USB connection to a computer with a web browser is all that is needed for configuration.

### Your advantages

- ✓ Future-proof 4G technology (LTE CAT1), simultaneous use of well-established 2G networks (GSM, GPRS, EDGE)
- ✓ Alerts via SMS in the field and, for example, via e-mail in the control room
- ✓ Message chain for sending an alert to the relevant service technician
- ✓ Alarm generation on voltage failure via SMS
- ✓ Free switching via phone call
- ✓ Cost control for prepaid cards
- ✓ Remote commands to avoid on-site servicing: switching, configuration commands, and logbook transmission
- ✓ Compact design also for domestic installations (4 HP, DIN 43880)
- ✓ Mounting on DIN rail or on the wall



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 592046
GTIN	4055626592046
Weight per Piece (excluding packing)	240.100 g
Custom tariff number	85176200
Country of origin	Germany

### Technical data

#### Dimensions

Width	72 mm
-------	-------

# SMS relay - TC MOBILE I/O X200-4G - 1038567

## Technical data

### Dimensions

Height	90 mm
Depth	62 mm

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C (SMS mode only, note the derating information in the technical documentation for data connection)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	0 % ... 95 %
Altitude	2000 m
Degree of protection	IP20

### General

Electromagnetic compatibility	Conformance with RED Directive 2014/53/EU
Net weight	240.1 g
Housing material	Polycarbonate
MTTF	674 Years (SN 29500 standard, temperature 25 °C, operating cycle 21 % (5 days a week, 8 hours a day))
	324 Years (SN 29500 standard, temperature 40 °C, operating cycle 34.25 % (5 days a week, 12 hours a day))
	130 Years (SN 29500 standard, temperature 40 °C, operating cycle 100 % (7 days a week, 24 hours a day))
Wireless licences	Europe

### Power supply

Supply voltage range	10 V DC ... 60 V DC
Max. current consumption	80 mA
Typical current consumption	50 mA (24 V DC)
Conductor cross section flexible max.	2.50 mm²
Conductor cross section flexible min.	0.20 mm²
Conductor cross section solid max.	2.50 mm²
Conductor cross section solid min.	0.20 mm²
Max. AWG conductor cross section, flexible	14
Min. AWG conductor cross section, flexible	24
Conductor cross section AWG max.	14
Conductor cross section AWG min.	24

### Interfaces

Interface 1	USB 2.0
Connection method	Mini-USB type B, 5-pos.
Transmission length	≤ 3 m (only for configuration and diagnostics)

### Wireless interface

Interface description	GSM / GPRS / EDGE / LTE (FDD)
Frequency	850 MHz (2 W (EGSM))
	900 MHz (2 W (EGSM))

# SMS relay - TC MOBILE I/O X200-4G - 1038567

## Technical data

### Wireless interface

	1800 MHz (1 W (EGSM))
	1900 MHz (1 W (EGSM))
	800 MHz (LTE B20)
	1800 MHz (LTE B3)
	2600 MHz (LTE B7)
GPRS	Multislot Class 33
EDGE	Multislot Class 33
LTE	CAT1
Country support	Europe

### Digital outputs

Output name	Relay output
Number of outputs	4
Contact type	N/O contact
Minimum switching voltage	100 mV
Maximum switching voltage	60 V DC
	30 V AC
Limiting continuous current	6 A
Switching capacity	100 W (Power Source PS2, $P_{out} \leq 100$ W)
Electrical service life	30000 cycles

### Digital inputs

Description of the input	Digital input
Number of inputs	4
Switching threshold "0" signal in reference to $U_N$	$\leq 0.3$
Switching threshold "1" signal in reference to $U_N$	$\geq 0.7$

### Analog inputs

Description of the input	Analog input
Number of inputs	2
Input signal	Current or voltage
Voltage input signal	0 V DC ... 60 V DC
Current input signal	0 mA ... 20 mA
	4 mA ... 20 mA (configurable)
Input impedance	600 k $\Omega$ (Voltage inputs)
	50 $\Omega$ (Current inputs)
Precision	$\pm 0.1$ %
Resolution	15 bit

### Conformance/approvals

Designation	CE
Identification	CE-compliant

## SMS relay - TC MOBILE I/O X200-4G - 1038567

### Technical data

#### Standards and Regulations

Electromagnetic compatibility	Conformance with RED Directive 2014/53/EU
Standards/regulations	EN 61000-4-2
Contact discharge	± 6 kV
Indirect discharge	± 6 kV
Standards/regulations	EN 61000-4-3
Frequency range	26 MHz ... 6 GHz
Standards/regulations	EN 61000-4-4
Comments	Criterion B
Standards/regulations	EN 61000-4-5
Signal	± 1 kV (Data line, asymmetrical)
Standards/regulations	EN 61000-4-6
Frequency range	0.15 MHz ... 80 MHz
Standards/regulations	EN 50360
	EN 50121-4


#### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Drawings

## SMS relay - TC MOBILE I/O X200-4G - 1038567


Connection diagram



Floating relay contacts

## SMS relay - TC MOBILE I/O X200-4G - 1038567


Diagram



Relay load curve DC

## SMS relay - TC MOBILE I/O X200-4G - 1038567


Diagram



Relay load curve AC

## SMS relay - TC MOBILE I/O X200-4G - 1038567

Schematic diagram




DIN rail mounting



## SMS relay - TC MOBILE I/O X200-4G - 1038567


Schematic diagram



Wall mounting

## SMS relay - TC MOBILE I/O X200-4G - 1038567


Schematic diagram



Front view

## SMS relay - TC MOBILE I/O X200-4G - 1038567


Schematic diagram



Insert the SIM card

## SMS relay - TC MOBILE I/O X200-4G - 1038567

Schematic diagram



Insert the SIM card

### Classifications

#### eCl@ss

eCl@ss 4.0	27250312
eCl@ss 4.1	27250312
eCl@ss 5.0	27242208
eCl@ss 5.1	27242200
eCl@ss 6.0	19179200
eCl@ss 7.0	19179290
eCl@ss 8.0	19179290
eCl@ss 9.0	27242608

#### ETIM

ETIM 3.0	EC000310
ETIM 4.0	EC000310
ETIM 5.0	EC001604
ETIM 6.0	EC001604
ETIM 7.0	EC001604

#### UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	43222604

## SMS relay - TC MOBILE I/O X200-4G - 1038567

### Classifications

#### UNSPSC

UNSPSC 18.0	32151602
UNSPSC 19.0	32151602
UNSPSC 20.0	32151602
UNSPSC 21.0	32151602

### Accessories

#### Accessories

##### Antenna

Antenna - TC ANT MOBILE WALL 5M - 2702273



Multiband cellular antenna with mounting bracket for outdoor installation, 5 m antenna cable with SMA circular connector, suitable for LTE/4G

---

##### Coaxial cable

Antenna cable - PSI-CAB-GSM/UMTS-10M - 2900981



Cellular antenna cable, 10 m in length, SMA (male) -> SMA (female), 50 ohm impedance

---

Antenna cable - PSI-CAB-GSM/UMTS- 5M - 2900980



Cellular antenna cable, 5 m in length, SMA (male) -> SMA (female), 50 ohm impedance

---

##### Power supply

Power supply unit - STEP-PS/ 1AC/24DC/0.5 - 2868596



Primary-switched STEP POWER power supply for DIN rail mounting, input: 1-phase, output: 24 V DC/0.5 A

## SMS relay - TC MOBILE I/O X200-4G - 1038567

### Accessories

#### Programming cable

USB cable - CABLE-USB/MINI-USB-3,0M - 2986135



USB connecting cable: USB plug type A to USB plug type Mini-B; length: 3 m

---

#### Surge protection for transceiver systems

Surge protection device - CSMA-LAMBDA/4-2.0-BS-SET - 2800491



Attachment plug with Lambda/4 technology as surge protection for coaxial signal interfaces. Connection: Male/female SMA connectors.