

FEATURES

- A supple and light glove, with cut level 4 resistance
- Anatomically designed to follow the natural curve of the hand and help reduce hand fatigue
- Excellent grip in both wet and dry environments
- High abrasion and tear resistance

DESCRIPTION

- Seamless nylon/glass fibre liner with a unique bi-polymer coated palm
- Breathable back of the hand to reduce perspiration and skin irritation
- Silicone free
- Elasticated wrist provides a secure fit
- Treated with Actifresh to kill bacteria and promote freshness
- Mottled grey and black colouring, suitable for the dirtiest of environments



TECHNICAL DATA

AVAILABLE SIZES 7/S • 8/M • 9/L • 10/XL • 11/XXL

PACKAGING 10/120
Pairs per pack/box

COLOUR OF LINER/COATING Grey/Black

TYPICAL APPLICATIONS

- Engineering
- Glass industries
- Component assembly
- Packaging
- Bottling or canning

Cat
CE II



EN 388 standard

Abrasion	4
Cut	4
Tear	3
Puncture	2



Recommendations For Use

- These gloves resist cut but are not cut proof. Do not use near moving machines if there is a risk of entanglement.
- Storage: Gloves should be ideally stored in cool, dry conditions in original packaging and away from direct sunlight.
- Cleaning/Maintenance: Both new and used gloves should be thoroughly inspected before being worn to ensure no damage is present. Gloves should not be left in contaminated condition if reuse is intended in which case gloves should be cleaned as far as possible. If appropriate, decontamination may take place under lukewarm water using laundry soap and detergent. Don't use chlorine bleaches.