



## Main

Range	TeSys
Device short name	LU6MB
Product or component type	Reverser block
Device mounting	Separate mounting
Device application	Motor control
[Ie] rated operational current	32 A
[Uc] control circuit voltage	48 V AC 50/60 Hz 48...72 V DC
Current consumption	2300 mA at 48 V AC I maximum while closing 2300 mA at 48...72 V DC I maximum while closing

## Complementary

[Ue] rated operational voltage	690 V AC power circuit
Network frequency	40...60 Hz
Inrush restraint duration	25 Ms AC 15 ms DC
Operating time	150 ms with change of direction 75 ms without change of direction
Standards	EN 60947-6-2 IEC 60947-6-2 UL 60947-4-1, with phase barrier CSA C22.2 No 60947-4-1, with phase barrier
Product certifications	CE[RETURN]UL[RETURN]CSA[RETURN]CCC[RETURN]EAC[RETURN]ASEFA[RETURN]
[Ui] rated insulation voltage	690 V conforming to IEC 60947-6-2 600 V conforming to UL 60947-4-1 600 V conforming to CSA C22.2 No 60947-4-1
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-6-2
Fixing mode	Clipped (DIN rail) Screw-fixed (plate)
Connections - terminals	Control circuit: screw clamp terminals 1 cable(s) 0.34...1.5 mm <sup>2</sup> (external diameter: 3 mm) flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 0.75...1.5 mm <sup>2</sup> (external diameter: 3 mm) flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 0.75...1.5 mm <sup>2</sup> (external diameter: 3 mm) rigid Control circuit: screw clamp terminals 2 cable(s) 0.34...1.5 mm <sup>2</sup> (external diameter: 3 mm) flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 0.75...1.5 mm <sup>2</sup> (external diameter: 3 mm) flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 0.75...1.5 mm <sup>2</sup> (external diameter: 3 mm) rigid Power circuit: screw clamp terminals 1 cable(s) 1...10 mm <sup>2</sup> (external diameter: 4 mm) rigid Power circuit: screw clamp terminals 1 cable(s) 1...6 mm <sup>2</sup> (external diameter: 4 mm) flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 2.5...10 mm <sup>2</sup> (external diameter: 4 mm) flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 1...6 mm <sup>2</sup> (external diameter: 4 mm) flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 1...6 mm <sup>2</sup> (external diameter: 4 mm) rigid Power circuit: screw clamp terminals 2 cable(s) 1.5...6 mm <sup>2</sup> (external diameter: 4 mm) flexible without cable end

Tightening torque	Control circuit: 0.8...1.2 N.m flat screwdriver 5 mm Control circuit: 0.8...1.2 N.m Philips No 2 screwdriver 5 mm Power circuit: 1.9...2.5 N.m flat screwdriver 6 mm Power circuit: 1.9...2.5 N.m Philips No 2 screwdriver 6 mm Power circuit: 1.9...2.5 N.m pozidriv No 2 screwdriver 6 mm
Width	45 mm
Height	115 mm
Depth	113 mm
Net weight	0.425 kg
Compatibility code	LU6MB

## Environment

IP degree of protection	IP20 conforming to IEC 60947-1 (front panel and wired terminals) IP20 conforming to IEC 60947-1 (other faces) IP40 conforming to IEC 60947-1 (front panel outside connection zone)
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-25...60 °C with LUCM -25...70 °C with LUCA, LUCB, LUCC, LUCD
Ambient air temperature for storage	-40...85 °C
Fire resistance	960 °C parts supporting live components conforming to IEC 60695-2-12 650 °C conforming to IEC 60695-2-12
Operating altitude	2000 m
Shock resistance	10 gn power poles open conforming to IEC 60068-2-27 15 gn power poles closed conforming to IEC 60068-2-27
Vibration resistance	2 gn (f= 5...300 Hz) power poles open conforming to IEC 60068-2-27 4 gn (f= 5...300 Hz) power poles closed conforming to IEC 60068-2-27
Resistance to electrostatic discharge	8 KV level 3, in open air conforming to IEC 61000-4-2 8 kV level 4, on contact conforming to IEC 61000-4-2
Resistance to radiated fields	10 V/m level 3 conforming to IEC 61000-4-3
Resistance to fast transients	2 KV class 3 serial link conforming to IEC 61000-4-4 4 kV class 4 all circuits except for serial link conforming to IEC 61000-4-4
Non-dissipating shock wave	1 KV serial mode conforming to IEC 60947-6-2 2 kV common mode conforming to IEC 60947-6-2
Immunity to radioelectric fields	10 V conforming to IEC 61000-4-6

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins