


D

C

B

A



LC CONN. MARK	LC CONN. MARK
A	B
B	A

NOTES:

- 1ATTENUATION ≤ 0.3 dB, MEASURED AT 1310 nm
ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
- 2RETURN LOSS ≥ 45 dB, IN MATED CONDITION
AGAINST REFERENCE CONNECTOR AT 1310 nm
- 3TUNED CONNECTORS
- 4CABLE INFORMATION:
 - CORE DIAMETER: 9/125 μm
 - OUTER JACKET DIAMETER: 1.8x3.6 mm
 - OUTER JACKET COLOUR: YELLOW
 - OUTER JACKET MATERIAL: LSZH
- 5

BLANK LABEL
- 6

INFORMATION ON LABEL
 - BARCODE
 - UNIQUE SERIAL NUMBER
 - TYCO ELECTRONICS PART NUMBER & ORDER NUMBER
 - ATTENUATION & RETURN LOSS AT 1310 nm

STANDARD LENGTHS ACCORDING TO
CUSTOMER DRAWING 1206850

PART NUMBER	"L" (meter)
X-2061308-Y	XY.0

6	FOAC INFORMATION LABEL	3
2	LC DUPLEX CONNECTOR, SINGLE MODE, BLUE	2
L	FOCAB 1.8MZ 9/125, YELLOW, LSZH	1
Qty	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DWN R. COOLEN 16OCT2009 CHK A. HENGELMOLEN 16OCT2009 APVD A. HENGELMOLEN 16OCT2009 PRODUCT SPEC APPLICATION SPEC WEIGHT — CUSTOMER DRAWING		Tyco Electronics Corporation 's-Hertogenbosch, Nederland NAME FIBER OPTIC LEAD 1.8MZ LC/DPX — LC/DPX SINGLE MODE 9/125 SIZE A2 CAGE CODE 00779 DRAWING NO C=2061308 RESTRICTED TO — SCALE NTS SHEET 1 OF 1 REV A