



TE Internal #: 3-1474644-1

Wire-to-Board, 16 Position, 2.54 mm [.1 in] Centerline, 76.2 mm [3 in] Length, Printed Circuit Board, Power, Wire-to-Board Jumpers & Shunts

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Jumpers & Shunts



Connector System: **Wire-to-Board**

Number of Positions: **16**

Centerline (Pitch): **2.54 mm [.1 in]**

Product Length: **76.2 mm [3 in]**

Connector & Contact Terminates To: **Printed Circuit Board**

Features

Product Type Features

Compatible With Discrete Wire Type	Solid
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Conductors	16
Number of Rows	1
Number of Positions	16

Electrical Characteristics

Operating Voltage	300 VAC
Impedance	117 Ω

Body Features

Jumper Insulation Material	Aramid Paper
----------------------------	--------------

Contact Features

Pin Arrangement (Right)	A
Pin Arrangement (Left)	A
Contact Current Rating (Max)	3 A

Housing Features

--	--



Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Wire Size	24 AWG
Product Length	76.2 mm[3 in]

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1-6437144-6
FSN-23.7A-12



TE Part # 1-1474644-2
FSN-23A-14



TE Part # 2-1474644-3
FSN-23A-9



TE Part # 8-6437125-5
FSN-23AB-14



TE Part # 1474644-9
FSN-23A-4



TE Part # 2205353-1
FSN-23A-11



TE Part # 4-1474644-0
FSN-23A-20

Customers Also Bought



TE Part #3-1474644-8
FSN-24A-14




TE Part #3-641239-6
06P MTA100 CONN ASSY BLU LF




TE Part #1879354-6
RR03 5% R51 AMMO




TE Part #3-2176392-9
RQ 1206 332K 0.1% 10PPM 5K RL



TE Part #284512-2
2 POS TERMI-BLOK HDR 900 POLAR



TE Part #215309-2
2X2P HV100 REC CON. TE, 8.5MM



TE Part #350491-1
093 PCB PIN PTBR



TE Part #9-2176400-7
3540 10K 1%



TE Part #2199337-5
ASS'Y FOR MICRO SIM H1.18 8POS (EMBOSS)



TE Part #3-641208-5
05P MTA156 HDR ASSY FL ST LF

Documents



Product Drawings

FSN-23A-16

English

Product Specifications

Product Specification

English

Agency Approvals

UL Report

English