


Geberit Mapress Copper bend with plain ends



Example image



TECHNICAL DATA

Product material Cu-DHP copper CW024A (EN 1412)

Art. no.	DN	d _ø mm	arc °	H cm	H1 cm	K cm	K1 max. cm
60905	25	28	15	4.3	11.9	0	7.6
60906	32	35	15	4.1	11.8	0	7.7
60907	40	42	15	4.7	13.7	0	9
60908	50	54	15	5.5	14.9	0	9.4
60935	25	28	30	4.8	12.4	0	7.6
60936	32	35	30	4.6	12.3	0	7.7

Art. no.	DN	d _ø mm	arc °	H cm	H1 cm	K cm	K1 max. cm
60937	40	42	30	5.4	14.4	0	9
60938	50	54	30	6.3	15.7	0	9.4
60875	25	28	45	4.5	11.8	0	7.3
60876	32	35	45	4.9	12.6	0	7.7
60877 Phasing out	40	42	45	5.7	14.7	0	9
60878	50	54	45	6.8	16.2	0	9.4
60955	25	28	60	6.1	13.7	0	7.6
60956	32	35	60	5.9	13.6	0	7.7
60957	40	42	60	6.9	15.9	0	9
60958 Phasing out	50	54	60	8.3	17.7	0	9.4
60082	12	15	90	5.1	11.8	0	6.7
60083	15	18	90	5.3	12.2	0	6.9

<i>Art. no.</i>	<i>DN</i>	<i>d_ø</i> <i>mm</i>	<i>arc</i> <i>°</i>	<i>H</i> <i>cm</i>	<i>H1</i> <i>cm</i>	<i>K</i> <i>cm</i>	<i>K1 max.</i> <i>cm</i>
60084	20	22	90	6	12.8	0	6.8
60085	25	28	90	6.5	14	0	7.5
60086	32	35	90	7.4	15.1	0	7.7
60087	40	42	90	8.6	17.6	0	9
60088	50	54	90	10.6	20	0	9.4