

product type designation



Antenna ANT795-6MP

ANT795-6MP antenna for WLAN (2.4/5/6 GHz), omnidirectional characteristic; including N-female plug: 5/8/8 dBi; IP65/67 (-40...+80 °C); Wi-Fi compliance and national approvals to be considered; mounting on wall or mast; scope of supply: 1x ANT795-6MP 1x mounting aid

suitability for operation

antenna for WLAN applications in the 2.4 / 5 and 6 GHz band

radio frequencies

type of wireless network / is supported	WLAN
operating frequency	
• for WLAN in 2.4 GHz frequency band	2.4 ... 2.5 GHz
• for WLAN in 5 GHz frequency band 1	4.94 ... 5925 GHz
• with WLAN in 6 GHz frequency band	5925 ... 7125 Hz

electrical data

antenna gain compared to spherical radiator	
• with linear radiation	typical maximum gain measured in open space
• of the WLAN antenna / in the 2.4 GHz frequency band	5 dB
• of the WLAN antenna / in the 5 GHz frequency band	8 dB
• of the WLAN antenna / in the 6 GHz frequency band	8 dB
impedance	50 Ω
polarization	linear, vertical
radiation characteristic	omnidirectional
standing wave ratio (VSWR) / maximum	2.5
radiating angle of the antenna	take the antenna diagram into account regarding the horizontal beam angle
• in the 2.4 GHz frequency band / horizontal	360°
• in the 5 GHz frequency band / horizontal	360°
number of electrical connections / of the antenna	1
type of electrical connection / of the antenna	N-Connector
design of plug-in connection	female
angle of inclination / downward / maximum	0°

mechanical data

material	
• of outer shell	UV-resistant white ASA plastic
color	white

ambient conditions

ambient temperature	
• during operation	-40 ... +85 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
protection class IP	IP67

design, dimensions and weights

width	97 mm
height	361 mm; incl. bracket
depth	64 mm
diameter	28.6 mm

net weight	200 g
fastening method	
• mast mounting	Yes
• wall mounting	Yes
• roof mounting	No
• directly on the device	No
product features, product functions, product components / general	
product feature / silicon-free	Yes
standards, specifications, approvals	
certificate of suitability	
• RoHS conformity	Yes
wireless approval	Current national approvals can be found on the Internet under www.siemens.com/funkzulassungen
reference code / according to IEC 81346-2:2019	TFB
last modified:	5/9/2025 