


## Fujitsu RAC and VRF to KNX Interface with binary inputs (to CN connector)

Item number: INKNXFGL001I000

The Fujitsu-KNX interface allows full bidirectional communication between Fujitsu RAC and VRF units and KNX installations. It has four potential-free binary inputs to integrate external devices (such as window contacts or presence detectors), with the corresponding internal functions available to help improve energy efficiency.



*Fujitsu to KNX - 1 indoor unit*

## Features and benefits

- ✓ **ETS configuration**  
The interface is configured using the ETS standard configuration tool software.
- ✓ **Multiple energy efficiency functions available**  
Timeout, open window, or occupancy energy-saving functions are available to reduce energy costs.
- ✓ **Total unit control and monitoring from KNX**  
Through internal variables, running hours counter (for maintenance purposes), and error indication.
- ✓ **AC unit control by both remote controller and KNX**  
The AC unit can be simultaneously controlled by the manufacturer's remote controller and KNX.
- ✓ **Compatible with all KNX thermostats in the market**  
All the required DPT objects to be compatible with all KNX thermostats in the market are available.
- ✓ **Smooth KNX thermostat integration**  
KNX thermostats are allowed to control the AC unit via the thermostat's temperature sensor.
- ✓ **Up to five scenes saved/executed from KNX**  
Up to five scenes can be saved and executed from KNX.
- ✓ **Compact dimensions, allowing inside installation**  
The interface can be quickly installed inside the AC unit thanks to its reduced dimensions.

# Fujitsu RAC and VRF to KNX Interface with binary inputs (to CN connector)



General	
Net Width (mm)	45
Net Height (mm)	21
Net Depth (mm)	59
Net Weight (g)	81
Packed Width (mm)	12
Packed Height (mm)	7
Packed Depth (mm)	9
Packed Weight (g)	87
Operating Temperature °C Min	0
Operating Temperature °C Max	70
Storage Temperature °C Min	-20
Storage Temperature °C Max	85
Power Consumption (W)	5.8
Input Voltage (V)	29 VDC
Power Connector	2-pole
Configuration	ETS
Capacity	1 Indoor unit.
Installation Conditions	This gateway is designed to be mounted inside an enclosure. If the unit is mounted outside an enclosure, precautions should always be taken to prevent electrostatic discharge to the unit. When working inside an enclosure (e.g., making adjustments, setting switches, etc.), typical anti-static precautions should always be followed before touching the unit.
AC Model Compatibility	Fujitsu RAC and VRF systems

# Fujitsu RAC and VRF to KNX Interface with binary inputs (to CN connector)



## General

Content of Delivery	Intesis Gateway, Installation Manual, AC Connection cable.
Housing Materials	Plastic
Warranty (years)	3 years
Packaging Material	Cardboard

## Identification and Status

Product ID	INKNXFGL001I000
Country of Origin	Spain
HS Code	8517620000
Export Control Classification Number (ECCN)	EAR99

## Physical Features

Connectors / Input / Output	KNX, HVAC port, Binary inputs (dry contact).
LED Indicators	KNX


## Certifications and Standards

ETIM Classification	EC001604
WEEE Category	IT and telecommunications equipment

# Fujitsu RAC and VRF to KNX Interface with binary inputs (to CN connector)



## Use Case



Integration example.