

Ø 4 mm connecting plugs

Test & Measureline | Test & Measurement

EN



Ø 4 MM SYSTEM


Connecting plug

Connecting plug K...4N-19


Insulated, Ø 4 mm, made of brass. Plugs with spring-loaded MULTILAM contact technology. With insulated grip. At rear with-

out or with two in-line Ø 4 mm rigid sockets accepting spring-loaded Ø 4 mm plugs.

KS-4N-19



KS2-4N-19



Order No.	Type	Rated voltage/current	Plug spacing		*Standard colors
64.4012-*	KS-4N-19	AC 30 V/32 A DC 60 V/32 A	19 mm	<div>Ni</div>	<div><div>20</div><div>21</div><div>22</div><div>23</div><div>24</div><div>25</div><div>26</div><div>27</div><div>28</div><div>29</div><div>30</div></div>
64.4010-*	KS2-4N-19	AC 30 V/32 A DC 60 V/32 A	19 mm	<div>Ni</div>	<div><div>20</div><div>21</div><div>22</div><div>23</div><div>24</div><div>25</div><div>26</div><div>27</div><div>28</div><div>29</div><div>30</div></div>



User information **i099**


www.staubli.com/electrical

Connecting plug SK...4N-19


Insulated, Ø 4 mm, made of brass. Plugs with spring-loaded MULTILAM contact technology and rigid insulating sleeves. With insulated grip. At rear without or with

in-line Ø 4 mm rigid sockets accepting spring-loaded Ø 4 mm plugs with rigid insulating sleeve.

SKS-4N-19



SKS2-4N-19



Order No.	Type	Rated voltage/current	Plug spacing		*Standard colors
66.4012-*	SKS-4N-19	1000 V, CAT II/32 A	19 mm	Ni CE c UL us	<div>20 21 22 23 24</div> <div>25 26 27 28 29</div> <div>30</div>
66.4010-*	SKS2-4N-19	1000 V, CAT II/32 A	19 mm	Ni CE c UL us	<div>20 21 22 23 24</div> <div>25 26 27 28 29</div> <div>30</div>



● Stäubli Units ○ Representatives/Agents

Global presence of the Stäubli Group

www.staubli.com