



MANU-ROLL

POLYCHOC WHEEL

STRONG POINTS

- For wet applications.
- Low starting effort.
- For smooth surfaces.



Materials handling castor

APPLICATIONS

Standard materials handling on hard surfaces and ones which are in good condition.

CASTOR ASSEMBLY: • Swivel or fixed. • Pressed steel. • Fastening by top plate. • Swivels on two rows of balls. • Bright zinc-plated protection.

WHEEL: • Polychoc: white polychoc one-piece wheel. • Plain bore. • Bolted axle.

LOCKING: • **MB** Meta-bloc: double-action adjustable rear brake. • Steel pedal.

Icon	Icon	Icon	Icon	Icon	Icon	Icon	Icon	Icon	Type	Icon	Code	EAN 13	
125	35	165	62	52	135x110	105x80	11	175			1,280	135 0507	339680 618050 1
											1,640	1 351 0507	339680 618051 8
											0,865	518 0507	339680 618052 5
150	38	191	62	50	135x110	105x80	11	175			1,450	135 0607	339680 618060 0
											1,825	1 351 0607	339680 618062 4
											0,995	518 0607	339680 618064 8
200	50	236	62	50	135x110	105x80	11	200			1,700	135 0807	339680 618080 8
											2,050	1 351 0807	339680 618082 2
											1,485	518 0807	339680 618084 6