

3GAA101520-BSJ



General Information

Product ID:	3GAA101520-BSJ
ABB Type Designation:	M3AA 100LB 2
Catalog Description:	No Description Available

Additional Information

ABB Type Designation: M3AA 100LB 2

Bearing: 6306-2Z/C3

Bearing NDE: 6205-2Z/C3

Country of Origin: Poland (PL)
Finland (FI)
China (CN)

Customs Tariff Number: 85015220

Electrical Data:

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	3.00 kW	2897 r/min	5.40 A	0.930	87.50 %	9.90 N·m	7.60
D	--	50 Hz	230 V	3.00 kW	2897 r/min	9.40 A	0.930	87.60 %	9.90 N·m	7.60
Y	--	50 Hz	415 V	3.00 kW	2904 r/min	5.10 A	0.920	87.60 %	9.90 N·m	8.20

Gross Weight: 36 kg

IC Class: IC411

IE Class Data (50 Hz): IE Class IE3
Full Load (100%) 87.5 %
Partial Load (75%) 88.5 %
Partial Load (50%) 88.6 %

IM Class: IMB5 IM3001

IP Class: IP55

Insulation Class: ICLF

Made To Order: No

Minimum Order Quantity: 1 piece

Order Multiple: 1 piece

Package Level 1 Units: 0 carton

Poles (High): 2

Product Name: 3-Phase squirrel cage motor

Product Net Weight: 31 kg

Quote Only: No

Replaced Product ID (OLD): 3GAA101612-BSJ

Selling Unit of Measure: piece

Stocked At (Warehouses): Central Stock Europe
Central Stock Nordic
Central Stock Spain
CSCNM
CSI

Temperature Class Default: --

Two Speed Motor: No

Voltage Code: S