




TE Internal #: T4162214004-005
M12 Cable Assembly, 4 Position, Cable Assembly Length 5 m [16.4 ft], Sensor/Actuator, A Code, M12 Plug End A, M12 Socket End B, Shielded, Double Ended
[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M12 A-Code Male to Female Double Ended Cable



Cable Assembly Length: 5 m [16.4 ft]
M8/M12 Application Type: **Sensor/Actuator**
Number of Positions: 4
Connector & Keying Code: **A**
Cable Assembly Type: **M12**

[All M12 A-Code Male to Female Double Ended Cable \(140\)](#)

Features

Product Type Features

Cable Assembly Type	M12
Cable Assembly (End A)	M12 Plug
Cable Assembly (End B)	M12 Socket

Configuration Features

Number of Positions	4
---------------------	---

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Body Features

Connector Color (End B)	Black
Jacket Material	PVC
Connector Color (End A)	Black
Conductor Material	Copper Alloy
Cable Color	Black



Wire Color (Base)	Brown, White, Blue, Black
Connector & Keying Code	A

Contact Features

Contact Current Rating (Max)	4 A
------------------------------	-----

Mechanical Attachment

Thread Size	M12 x M12
Connector Orientation (End A)	Right Angle
Connector Orientation (End B)	Right Angle

Housing Features

Housing Material	Nylon GF
------------------	----------

Dimensions

Wire Size	22 AWG
-----------	--------

Operation/Application

M8/M12 Application Type	Sensor/Actuator
Shielded	Yes

Other

Field Serviceable	Yes
Cable Assembly Length	5 m[16.4 ft]
Cable Assembly Configuration	Double Ended

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (1.9% in 8816659722) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T4162114004-005
RPC-M12-4MS-5.0SH-M12-4FR-PVC

Customers Also Bought



TE Part #TRA6927M3PW-001
OMNI,DB,Ph,698/1710 MHz WHT,3 dBi,100W,



TE Part #0462-201-20141
SOC, SOLID, SIZE 20, 20AWG, NI



TE Part #K1060542
Relay 26-55-710




TE Part #T4162113004-001
RPC-M12-4MS-0.5SH-M12-4FS-PVC



TE Part #58529-1
PRO-CRIMPER III TOOL AMPSEAL



TE Part #776164-1
35POS,AMPSEAL,SOC HSG ASSY,SLD, COD 1



TE Part #K1162382
CIRRUS-FWD-MCU_Redesign 89-03-002

Documents

Product Drawings
RPC-M12-4MR-5.0SH-M12-4FR-PVC



English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T4162214004-005_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T4162214004-005_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T4162214004-005_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

M12 connection application specification

English

Agency Approvals

UL

English