



**Part Number :** [26202096](#)  
**Product Description :** KK 396 Wire-to-Board  
Header, Vertical Round Pin, 9 Circuits, Tin (Sn) Plating,  
with Mating Pin Length of 32.51mm (1.28")  
**Series Number :** 3192  
**Status :** Active  
**Product Category :** PCB Headers and Receptacles  
**Engineering Number :** 319209F



## Documents & Resources

### Drawings


- [026202096 sd.pdf](#)
- [PK-3192-001-001.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)
- [Symbol and Footprint \(Multi-Format\)](#)
- [SYM-26-20-2091-001.zip](#)

### Specifications

- [PS-99020-0087-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	PCB Headers and Receptacles
Series	3192
Description	KK 396 Wire-to-Board Header, Vertical Round Pin, 9 Circuits, Tin (Sn) Plating, with Mating Pin Length of 32.51mm (1.28")
Application	Board-to-Board, Power, Wire-to-Board
Component Type	PCB Header
Product Name	KK 396
UPC	756054213889

### Agency

UL	E29179
----	--------

### Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	250V

### Physical

Breakaway	No
Circuits (Loaded)	9
Circuits (maximum)	9
Color - Resin	Natural
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-2
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	4.717/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.99mm
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Temperature Range - Operating	See Product Specification
Termination Interface Style	Through Hole

## Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	235

---

**Mates With / Use With**

**Mates with Part(s)**

Description	Part Number
KK 3.96mm Single Row Crimp Housings	<u>3069</u>