



## Main

|                           |                     |
|---------------------------|---------------------|
| Range of product          | Odace               |
| Product or component type | Rocker centre plate |
| Device application        | Switch              |
| Type of packing           | Plastic bag         |
| Quantity per set          | Set of 10           |

## Complementary

|                               |   |
|-------------------------------|---|
| Device mounting               | Flush   |
| Number of rocker              | 1   |
| Fixing mode                   | Clip-in   |
| Material                      | Thermoplastic ABS-UV stabilised: cover plate  |
| Diameter                      | 51 mm   |
| Depth                         | 8.5 mm  |
| Net weight                    | 0.003 kg  |
| Targeted channel              | Professional  |
| Resistance to chemical agents | Resistant to alcohol (70 %)<br>Resistant to alcohol (96 %)<br>Resistant to A-Lactic Acid<br>Resistant to diluted quaternary ammonium<br>Resistant to diluted bleach<br>Resistant to diluted ammonia<br>Resistant to soapy water<br>Resistant to crystal cleaner<br>Resistant to hydrogen peroxide 10 volumes<br>Resistant to hexane |

## Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| Ambient air temperature for storage   | -5...50 °C                  |
| Ambient air temperature for operation | 5...45 °C                   |
| Standards                             | EN 60669-1<br>2006/95/EEC   |
| Product certifications                | LCIE: NF 619318A<br>N<br>NF |
| IK degree of protection               | IK04                        |
| IP degree of protection               | IP21D                       |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | No need of specific recycling operations      |