

Parker Product Datasheet



The main function of Ermeto DIN tube to tube high pressure hydraulic tube fittings is to connect different numbers of tubes. This broad range of fittings is available in steel and in stainless steel.

PART NUMBER: SV28ZLCF

SHAPE: Straight

PRODUCT STYLE: Bulkhead

CONNECTION 1 SIZE: 28 mm (O.D.)

BODY MATERIAL: Steel

CONNECTION 1 TYPE: Male 24° Cone

ACCESSORIES INCLUDED: Pre-assembled with EO-2 Functional Nut

CONNECTION 2 TYPE: Male 24° Cone

CONNECTION 2 SIZE: 28 mm (O.D.)

PRODUCT OVERVIEW

The main function of Ermeto DIN tube to tube high pressure hydraulic tube fittings is to connect different numbers of tubes. This broad range of Ermeto DIN tube to tube high pressure hydraulic tube fittings, types G, GR, W, T, TR, K, SV, up to WSV is available in steel and in a stainless steel version. Depending on the specific application, the fittings can be delivered with cutting ring (EO-PSR or DPR) or elastomeric seal (EO-2).

Markets:

- Automotive
- Defence
- Energy
- Environment

- Industrial
- Infrastructure
- Machine Tools
- Material Handling
- Mobile
- Oil and Gas
- Power Generation
- Process
- Transportation
- Water

Applications:
Suitable for general hydraulic applications.

Features/ benefits:

- Steel and Stainless steel fittings have a high corrosion resistance to aggressive media and environmental influences. These features extend the range of applications.
- High pressure: Ermeto DIN tube to tube high pressure hydraulic tube fittings can be used in applications of up to 800 bar (S series) and 500 bar (L series), so that the fittings can be used in a wide range of applications.

TECH SPECIFICATIONS

DIVISION	High Pressure Connectors Europe Division
DIVISION	High Pressure Connectors Europe Division
MAXIMUM OPERATING PRESSURE	250 bar
FOR FLUID TYPE	Chemicals
FOR FLUID TYPE	Hydraulic Fluids
FOR FLUID TYPE	Gases
FOR FLUID TYPE	Fuels
FOR FLUID TYPE	Steam
INDUSTRY	Material Handling
INDUSTRY	Construction
INDUSTRY	Marine

INDUSTRY	Industrial Manufacturing Equipment
INDUSTRY	Automotive
INDUSTRY	Agriculture
INDUSTRY	Transportation
SPECIFICATIONS MET	ISO 8434
SPECIFICATIONS MET	DIN
SHAPE	Straight
APPLICATION	Hydraulics
APPLICATION	Chemical Transfer
APPLICATION	Fuel Transfer
APPLICATION	Packaging
APPLICATION	Oilfield
APPLICATION	Mobile Equipment
BRAND	Ermeto
TECHNOLOGY	Fluid & Gas Handling
PRODUCT STYLE	Bulkhead
CONNECTION 1 SIZE	28 mm Tube O.D.
BODY MATERIAL	Steel
CONNECTION 1 TYPE	Male
CONNECTION 1 TYPE	24° Cone
PRODUCT SERIES	EO Light
PRODUCT TYPE	Hydraulic DIN Fittings
SEAL MATERIAL	n/a
CONFIGURATION	Tube to Tube
ACCESSORIES INCLUDED	Pre-assembled with EO-2 Functional Nut
CONNECTION 2 TYPE	24° Cone
CONNECTION 2 TYPE	Male

CONNECTION 2 SIZE	28 mm Tube O.D.
MAXIMUM AMBIENT TEMPERATURE	300 °C
MAXIMUM AMBIENT TEMPERATURE	572 °F
MINIMUM AMBIENT TEMPERATURE	-40 °C
MINIMUM AMBIENT TEMPERATURE	-40 °F
MAXIMUM FLUID TEMPERATURE	572 °F
MAXIMUM FLUID TEMPERATURE	300 °C
MINIMUM FLUID TEMPERATURE	-40 °F
MINIMUM FLUID TEMPERATURE	-40 °C
SEAL TYPE	Sealing Edge