




RoHS Compliant

REV	SIGN	DATE	DESCRIPTION	APPROVER
		2024.06.25	Initial Release	LENA
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

- Material:
- Item ① Terminal Body: PA66,
 - Item ② Terminal lever: PBT ,
 - Item ③ Terminal Cover: PA66 ,
 - Item ④ Spring: Stainless
 - Item ⑤ Terminal Contact: Copper alloy,

- Electrical:
- | | | | |
|--------------------------|------------------|---------|---------|
| UL1059 | Group B.G | Group D | Group F |
| ●Voltage rating: | 300 V | 300V | 250V |
| ●Current rating: | 16A | 10A | 16A |
| ●Wire range: | | | |
| Solid wire: | 24-12AWG | | |
| Stranded wire: | 24-12AWG | | |
| ●Wire strip length: | 11-13 mm | | |
| ●Withstanding Voltage: | 1.6KV AC | | |
| ●Insulation Resisance: | DV500V 500MΩ min | | |
| ●Operating temperature: | -20℃ to +105℃ | | |
| ●Assembling temperature: | -5℃ to +105℃ | | |
| ●Safety Approval: | cULus | | |

Part No. QT xx A BI x x V xxxx G

- | | |
|--------------|---------------------------|
| NO. OF POLES | RoHS compliant |
| 02: 2 POLES | (lead<4%) |
| 03: 3 POLES | In copper Alloy |
| | |
| 24: 24 POLES | 00x0: "@" Logo (Standard) |
| | 00xA: "ANYTEK" Mark |
| | Any special item by |
| | customer request. |
| | please contact sales |
| | department. |
- | | |
|----------------------|----------------------|
| Body color | Lever color |
| 0: Black | 0: Black |
| 1: Natural color | 1: Natural color |
| 2: Red | 2: Red |
| 3: Orange | 3: Orange (標準色) |
| 4: Yellow | 4: Yellow |
| 5: Green (RAL6018/T) | 5: Green (RAL6018/T) |
| 6: Blue | 6: Blue |
| 8: Grey (標準色) | 8: Grey |
| 9: White | 9: White |
| C: Green | C: Green |
| (RAL 6018/U) | (RAL 6018/U) |

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	QT series 90D pitch 5.0mm.Behind Foot near Side Cover Interlace Soldering Foot						
PART NO.	QTxxABlxxVxxxxG			DWG NO.	8QT0011		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
Roy	Roy	Lena	Lena		UNIT: mm	X.	±0.50
2024.11.07	2024.11.07	2024.06.25	2024.06.25		SCALE: 2:1	X.X	±0.30
					REV.: A0	X.XX	±0.10
				SHEET: 01/01		X*	±1°