

Eaton 265901

Catalog Number: 265901

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 4p, 630A, 400A in 4th pole, H3-4-AE630/400



General specifications

Product Name	Catalog Number
Eaton Moeller series NZM molded case circuit breaker electronic	265901
	EAN
	4015082659011
Product Length/Depth	Product Height
166 mm	275 mm
Product Width	Product Weight
185 mm	8.4 kg
Compliances	Certifications
RoHS conform	IEC
	IEC/EN 60947

Product specifications

Type

Circuit breaker

Special features

Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn})

Rated current = rated uninterrupted current: 630 A

Reduced neutral conductor protection

Set value in neutral conductor is synchronous with set value I_r of main pole.

R.m.s. value measurement and "thermal memory"

Terminal capacity hint: Up to 240 mm² can be connected depending on the cable manufacturer.

Application

Use in unearthed supply systems at 690 V

Amperage Rating

630 A

Voltage rating

690 V - 690 V

Circuit breaker frame type

NZM3

Features

Motor drive optional

Protection unit

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Resources

Brochures

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Characteristic curve

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-045.eps](#)

[eaton-circuit-breaker-let-through-current-nzm-mccb-characteristic-curve.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-033.eps](#)

Drawings

[eaton-circuit-breaker-nzm-mccb-dimensions-021.eps](#)

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps](#)

eCAD model

[ETN.265901.edz](#)

Installation instructions

[eaton-circuit-breaker-basic-device-nzmn-b-il01208009z.pdf](#)

Installation videos

[The new digital NZM Range](#)

[Introduction of the new digital circuit breaker NZM](#)

mCAD model

[DA-CS-nzm3_4p](#)

[DA-CD-nzm3_4p](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Pollution degree

3

Mounting Method

Built-in device fixed built-in technique

Fixed

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Equipment heat dissipation, current-dependent

178.61 W

Utilization category

A (IEC/EN 60947-2)

Isolation

500 V AC (between auxiliary contacts and main contacts)

300 V AC (between the auxiliary contacts)

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

40 °C

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Protection against direct contact

Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110

Degree of protection

IP20

IP20 (basic degree of protection, in the operating controls area)

Direction of incoming supply

As required

Electrical connection type of main circuit

Screw connection

Current rating of neutral conductor

60% of phase conductor

400 A

Lifespan, mechanical

15000 operations

Overvoltage category

III

Degree of protection (IP), front side

IP66 (with door coupling rotary handle)

IP40 (with insulating surround)

Degree of protection (terminations)

IP10 (tunnel terminal)

IP00 (terminations, phase isolator and strip terminal)

Number of poles

Four-pole

Terminal capacity (copper strip)

Max. 10 segments of 24 mm x 1 mm + 5 segments of 24 mm x 1 mm

Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1 mm at rear-side connection (punched)

10 segments of 50 mm x 1 mm (2x) at rear-side width extension

Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched)

Max. 8 segments of 24 mm x 1 mm (2x) at box terminal

Min. 6 segments of 16 mm x 0.8 mm at box terminal

Lifespan, electrical

2000 operations at 690 V AC-3

3000 operations at 690 V AC-1

5000 operations at 415 V AC-1

2000 operations at 415 V AC-3

5000 operations at 400 V AC-1

2000 operations at 400 V AC-3

Functions

System and cable protection

Shock resistance

20 g (half-sinusoidal shock 20 ms)

Position of connection for main current circuit

Front side

Rated operational current for specified heat dissipation (I_n)

630 A

Release system

Electronic release

Short-circuit total breaktime

< 10 ms

Rated short-time withstand current ($t = 0.3$ s)

3.3 kA

Rated short-time withstand current ($t = 1$ s)

3.3 kA

Short-circuit release non-delayed setting - max

5040 A

Short-circuit release non-delayed setting - min

1260 A

Terminal capacity (control cable)

0.75 mm² - 1.5 mm² (2x)

0.75 mm² - 2.5 mm² (1x)

Terminal capacity (copper busbar)

Min. 20 mm x 5 mm direct at switch rear-side connection

Max. 10 mm x 50 mm (2x) at rear-side width extension

Max. 30 mm x 10 mm + 30 mm x 5 mm direct at switch rear-side connection

M10 at rear-side screw connection

Terminal capacity (copper solid conductor/cable)

16 mm² (1x) at tunnel terminal

16 mm² (2x) direct at switch rear-side connection

16 mm² (1x) direct at switch rear-side connection

16 mm² (2x) at box terminal

300 mm² (2x) at rear-side width extension

Terminal capacity (aluminum solid conductor/cable)

16 mm² (1x) direct at switch rear-side connection

10 mm² - 16 mm² (2x) direct at switch rear-side connection

16 mm² (1x) at tunnel terminal

Terminal capacity (copper stranded conductor/cable)

35 mm² - 240 mm² (1x) at box terminal
16 mm² - 185 mm² (1x) at 1-hole tunnel terminal
25 mm² - 120 mm² (2x) at box terminal
25 mm² - 240 mm² (2x) direct at switch rear-side connection
50 mm² - 240 mm² (2x) at 2-hole tunnel terminal
25 mm² - 240 mm² (1x) direct at switch rear-side connection

Terminal capacity (aluminum stranded conductor/cable)

25 mm² - 120 mm² (2x) direct at switch rear-side connection
25 mm² - 120 mm² (1x) direct at switch rear-side connection
50 mm² - 240 mm² (1x) at 2-hole tunnel terminal
50 mm² - 240 mm² (2x) at 2-hole tunnel terminal
25 mm² - 185 mm² (1x) at tunnel terminal

Handle type

Rocker lever

Short delay current setting (I_{sd}) - max

0 A

Short delay current setting (I_{sd}) - min

0 A

Instantaneous current setting (I_i) - max

5040 A

Instantaneous current setting (I_i) - min

1260 A

Number of operations per hour - max

60

Overload current setting (I_r) - max

630 A

Overload current setting (I_r) - min

315 A

Overload current setting (I_r)

200 A - 400 A

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 230 V, 50/60 Hz

150 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 400/415 V, 50/60 Hz

150 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 440 V, 50/60 Hz

130 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 525 V, 50/60 Hz

33 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 690 V, 50/60 Hz

9 kA

Rated short-circuit making capacity I_{cm} at 400/415 V, 50/60 Hz

330 kA

Rated short-circuit making capacity I_{cm} at 440 V, 50/60 Hz

286 kA

Rated short-circuit making capacity I_{cm} at 525 V, 50/60 Hz

143 kA

Rated short-circuit making capacity I_{cm} at 690 V, 50/60 Hz

74 kA

Standard terminals

Screw terminal

Optional terminals

Box terminal. Connection on rear. Tunnel terminal

Rated short-circuit making capacity I_{cm} at 240 V, 50/60 Hz

330 kA

Rated impulse withstand voltage (U_{imp}) at auxiliary contacts

6000 V

Rated impulse withstand voltage (U_{imp}) at main contacts

8000 V

Rated insulation voltage (U_i)

1000 V AC