

# SOT223 NPN SILICON PLANAR HIGH CURRENT (HIGH PERFORMANCE) TRANSISTORS

ISSUE 2 - OCTOBER 1995


## FEATURES

- \* Extremely low equivalent on-resistance;  $R_{CE(sat)}$  44m $\Omega$  at 5A
- \* 6 Amps continuous current, up to 20 Amps peak current
- \* Very low saturation voltages
- \* Excellent  $h_{FE}$  characteristics specified up to 10 Amps

FZT851  
FZT853

PARTMARKING DETAILS - DEVICE TYPE IN FULL

COMPLEMENTARY TYPES - FZT851 FZT951  
FZT853 FZT953



## ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	FZT851	FZT853	UNIT
Collector-Base Voltage	$V_{CBO}$	150	200	V
Collector-Emitter Voltage	$V_{CEO}$	60	100	V
Emitter-Base Voltage	$V_{EBO}$	6	6	V
Peak Pulse Current	$I_{CM}$	20	10	A
Continuous Collector Current	$I_C$	<b>6</b>	<b>6</b>	A
Power Dissipation at $T_{amb}=25^\circ\text{C}$	$P_{tot}$	<b>3</b>	<b>3</b>	W
Operating and Storage Temperature Range	$T_j:T_{stg}$	-55 to +150		°C

\*The power which can be dissipated assuming the device is mounted in a typical manner on a P.C.B. with copper equal to 4 square inch minimum

**ELECTRICAL CHARACTERISTICS  $T_{amb} = 25^\circ C$  (at unless otherwise stated)**

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS.
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	200	300		V	$I_C=100\mu A$
Collector-Emitter Breakdown Voltage	$V_{(BR)CER}$	200	300		V	$I_C=1\mu A$ , $R_B \leq 1k\Omega$
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	100	120		V	$I_C=10mA^*$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	6	8		V	$I_E=100\mu A$
Collector Cut-Off Current	$I_{CBO}$			10 1	nA $\mu A$	$V_{CB}=150V$ , $T_{amb}=25^\circ C$ $V_{CB}=150V$ $T_{amb}=100^\circ C$
Collector Cut-Off Current	$I_{CER}$ $R \leq 1k\Omega$			10 1	nA $\mu A$	$V_{CB}=150V$ , $T_{amb}=25^\circ C$ $V_{CB}=150V$ $T_{amb}=100^\circ C$
Emitter Cut-Off Current	$I_{EBO}$			10	nA	$V_{EB}=6V$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$		14 100	50 150 340	mV mV mV	$I_C=0.1A$ , $I_B=5mA^*$ $I_C=2A$ , $I_B=100mA^*$ $I_C=5A$ , $I_B=500mA^*$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$			1250	mV	$I_C=5A$ , $I_B=500mA^*$
Base-Emitter Turn-On Voltage	$V_{BE(on)}$			1100	mV	$I_C=5A$ , $V_{CE}=2V^*$
Static Forward Current Transfer Ratio	$h_{FE}$	100 100 50 20	200 200 100 30	300		$I_C=10mA$ , $V_{CE}=2V$ $I_C=2A$ , $V_{CE}=2V^*$ $I_C=4A$ , $V_{CE}=2V^*$ $I_C=10A$ , $V_{CE}=2V^*$
Transition Frequency	$f_T$		130		MHz	$I_C=100mA$ , $V_{CE}=10V$ $f=50MHz$
Output Capacitance	$C_{obo}$		35		pF	$V_{CB}=10V$ , $f=1MHz$
Switching Times	$t_{on}$ $t_{off}$		50 1650		ns ns	$I_C=1A$ , $V_{CC}=10V$ $I_{B1}=I_{B2}=100mA$ ,

\*Measured under pulsed conditions. Pulse width=300μs. Duty cycle ≤2%

Spice parameter data is available upon request for this device

# FZT853

## TYPICAL CHARACTERISTICS

