



Main

Range of product	Acti 9
Product name	Acti 9 iPRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	IPRD65r
Device application	Distribution
Poles description	1P + N
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Earthing system	TN-S TT

Complementary

Surge arrester class type	Type 2
Surge arrester technology	MOV + GDT
[Ue] rated operational voltage	230/400 V AC (+/- 10 %) at 50/60 Hz
[In] nominal discharge current	Common mode: 20 kA (L/PE) Common mode: 20 kA (N/PE) Differential mode: 20 kA (L/N)
[Imax] maximum discharge current	Common mode: 65 kA L/PE Common mode: 65 kA N/PE Differential mode: 65 kA L/N
[Uc] maximum continuous operating voltage	Common mode: 260 V N/PE Common mode: 350 V L/PE Differential mode: 350 V L/N
Maximum [Up] voltage protection level	Common mode <1.5 kV type 2 N/PE Differential mode <1.5 kV type 2 L/N
[Ut] temporary overvoltage	337 V L/N 5 s withstand 1200 V N/PE 200 ms safe failure mode 442 V L/PE 5 s withstand 1453 V L/PE 200 ms safe failure mode
Disconnecter device type	Associated circuit breaker iC60N 50 A curve C - Icu 10 kA Associated circuit breaker iC60H 50 A curve C - Icu 15 kA Associated circuit breaker NG125N 50 A curve C - Icu 25 kA Associated circuit breaker NG125H 100 A curve C - Icu 36 kA Associated circuit breaker NG125L 100 A curve C - Icu 50 kA Associated fuse gG 80 A - Icu 50 kA
[Iscsr] short-circuit current rating	50 kA
Signalling circuit voltage	0.25 A/250 V AC 50/60 Hz
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4
Height	85 mm
Width	36 mm
Depth	69 mm
Net weight	0.238 kg
Colour	White (RAL 9003)
Response time	<= 25 ns
[Ipe] Ground residual current	0.003 MA 0.6 MA

Connections - terminals	Tunnel type terminal (downside) 2.5...35 mm ² Tunnel type terminal (upside) 2.5...35 mm ²
Tightening torque	2.5 N.m

Environment

Standards	EN 61643-11:2012 IEC 61643-11:2011
Product certifications	CE
Quality labels	NF KEMA-KEUR
IP degree of protection	IP40 on front face: conforming to IEC 60529 IP20 built-in: conforming to IEC 60529
IK degree of protection	IK03 conforming to IEC 62262
Relative humidity	5...95 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------