



Relays & Contactors > Relay Accessories



Relay Socket Type: **Printed Circuit Board**

Pole Configuration: **2**

Relay Accessory Type: **Socket**

Features

Product Type Features

Relay Accessory Type	Socket
----------------------	--------

Contact Features

Terminal Style	PC
Relay Socket Type	Printed Circuit Board
Pole Configuration	2

Termination Features

Number of Pins	11
Termination Post & Tail Length	35 mm

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #5555140-1
MJ,LPF,R/A,6P/6C,SHLD,PNL GRD




TE Part #3-1825059-7
ADF08S04=DIP SWT,FLUSH,SMT-GW




TE Part #3-2176326-7
CRGP 0603 10K 1%




TE Part #3-1625890-2
2W SM M/OX 5% 22K




TE Part #8-215079-4
MICRO-MATCH FOB.14P




TE Part #NB10966001
ATUM-4/1-0-55MM




TE Part #282834-8
TERMI-BLOK PCB MOUNT, 90 8P.



TE Part #1-207532-0
SKT HDR ASSY,24P,MMATE LF



TE Part #215447-5
2X 5P MOD2 STIFTLEI



TE Part #5747091-2
09 RCPT ACT PIN/MS MED SCRLK

Documents

- CAD Files
- Customer View Model
- ENG_CVM_CVM_2-1393844-3_A1.2d_dxf.zip
- English
- 3D PDF



3D

Customer View Model

[ENG_CVM_CVM_2-1393844-3_A1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1393844-3_A1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Power Relay RM2/3/7](#)

English

[Accessories - Power Relay RM](#)

English

Product Specifications

[Definitions General Purpose Relays](#)

English