

## HR140DWAE1

Battery Type	Lithium-ion
Voltage	10.8 v
Impact energy	1.0 J
Capacity in Concrete	14 mm
Capacity in Steel	10 mm
Capacity in Wood	13 mm
Impacts per minute	0 - 4900 ipm
Vibration K factor	1.5 m/sec <sup>2</sup>
Net weight	1.9 - 2.6 kg
No Load Speed	0 - 850 rpm
Vibration: Hammer Drilling	6.5 m/sec <sup>2</sup>
Noise sound pressure	84 dB(A)
Noise K factor	3 dB(A)
Noise sound power	95 dB(A)
Battery quantity (4.0Ah)	2
Vibration: Drilling into metal	3.0 m/sec <sup>2</sup>



**STANDARD EQUIPMENT:** 197396-9 Battery BL1021B, DC10WD 12Vmax Standard Charger, Side handle, Hammer grease, Depth stop, Cloth, Carry case, 65 piece accessory set

- 2-mode operation: Rotary only and Rotary hammer
- Variable speed control by trigger
- Forward / reverse rotation
- LED job light
- One touch sliding chuck for easy bit installation and removal.
- Compact and lightweight design
- Vibration absorbing housing.