

## M12 A-cod 4-Pol an/st m/f PUR. 3,0 m



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 21 34 868 5491 030  |
| Specification      | M12 A-cod 4-Pol an/st m/f PUR. 3,0 m  |
| HARTING eCatalogue | <a href="https://harting.com/21348685491030">https://harting.com/21348685491030</a> |

### Identification

|               |                                 |
|---------------|---------------------------------|
| Category      | System cabling                  |
| Series        | Circular connectors M12         |
| Element       | Cable assemblies                |
| Specification | Pre-assembled on both sides     |
| Connector 1   | M12 A-coding<br>Male Angled     |
| Connector 2   | M12 A-coding<br>Female Straight |
| Type of cable | Copper cable (round)            |

### Version

|                 |                         |
|-----------------|-------------------------|
| Cable length    | 3 m                     |
| Number of cores | 4                       |
| Core structure  | 4x 0.34 mm <sup>2</sup> |
| Coding          | A-coding                |

### Material properties

|                  |                    |
|------------------|--------------------|
| Material (cable) | PUR (polyurethane) |
| Colour (cable)   | Black              |

### Commercial data

|                   |         |
|-------------------|---------|
| Packaging size    | 1       |
| Net weight        | 115 g   |
| Country of origin | Czechia |



**Pushing Performance**  
Since 1945

## Commercial data

|                                |   |
|--------------------------------|---|
| European customs tariff number | 85444290                                |
| GTIN                           | 5713140265448                           |
| eCl@ss                         | 27060311 Assembled sensor actuator-line |
| ETIM                           | EC002599                                |
| UNSPSC 24.0                    | 26121604                                |